

TEKNISK SPECIFIKATION TECHNICAL SPECIFICATION TECHNISCHE SPECIFIKATION		MASCOT WORKWEAR	
Kvalitet / Quality / Qualität: 154 (Industry)	Dato / Date / Datum: 13.10.2010		
			Standard / Method / Standard
Vægt / Weight / Gewicht	g/m ²	260	EN 12127
Komposition / Composition / Gewebemischung	%	65/35 pes/co	
Konstruktion / Construction / Webkonstruktion	2/2 panama (canvas)		
STYRKE / PHYSICAL PROPERTIES / FESTIGKEIT			
Slidstyrke / Abrasion resistance / Strapazierfähigkeit (Mindestwert) 12KPA	t	>65.000	EN ISO 12947-2
Brudstyrke, kæde / Tensile, warp/ Bruchfestigkeit, Kette (Mindestwert)	N.	1500	EN ISO 13394-1
Brudstyrke skud / Tensile, weft Bruchfestigkeit, Schuss (Mindestwert)	N.	950	EN ISO 13394-1
Rivstyrke, kæde / Tearing strength, warp/ Reissfestigkeit, Kette (Mindestwert)	N.	60	ISO 4674/A1
Rivstyrke, skud / Tearing strength, weft/ Reissfestigkeit, Schuss (Mindestwert)	N.	50	ISO 4674/A1
FARVEÆGTHEDER / COLOUR FASTNESS / FARBECHTHEIT			
Vaskeægthed / Fastness to washing / Waschechtheit staining on CO/PES	Note	4-5	ISO 105-C06
Svedægthed / Fastness to perspiration / Schweissechtheit	Note	4-5	ISO 105-E04
Lysægthed / Fastness to light / Lichtechtheit	Note	>5	ISO 105-B02
Gnidægthed, våd / Fastness to rubbing, wet / Reibechtheit, nass (Kette/Schuss)	Note	3	ISO 105-X12
Gnidægthed, tør / Fastness to rubbing, dry / Reibechtheit, trocken (Kette/Schuss)	Note	4	ISO 105-X12
GENERELLE EGENSKABER / CHARACTERISTICS IN GENERAL / ALLGEMEINE EIGENSCHAFTEN			
Dimensionsstabilitet / Dimensional stability / Dimensionsstabilität 5x75°c	%	-1,7	ISO 15797, proc. 8B
Vandsøjle / Water resistance / Wassersäule	mm H ₂ O		ISO 20811
Åndbarhed / Water vapour permeability / Åtmungsaktivitet	g/m ² /24 hrs		CUP METHOD
Finish / Finish / Ausführung			
Certifikater / Certificates / Zertifikate	 Indhold af sundhedsskadelige stoffer kontrolleret		
Vaskesymboler/Landry symbols/ Pflegesymbole			
Bemærkninger / Remarks / Bemerkungen:			