Shock-Safe Fuseholder, 5 x 20 / 6.3 x 32 mm, Slotted Cap









Socket with Slotted Cap Caps must be ordered separately (see accessories)

Socket with Slotted Cap (grey)

Socket with Slotted Cap

Socket with Fingergrip Cap

250 VAC · 4W/10 A (VDE) · 600 VAC/DC · 20 A (UL/CSA)

See below:

Approvals and Compliances

Description

- Quick-conntect or solder terminals

Weblinks

pdf data sheet, html datasheet, General Product Information, Distributor-Stock-Check, Accessories, Detailed request for product, Microsite

Technical Data	
Shock-Safe Category	PC2
Fuse-Link	5 x 20 / 6.3 x 32 mm
Mounting	Panel mount, Front Side
Attachment	Fixing Nut
Terminal	Solder / Quick-Connect 4.8 x 0.5 mm
Rated Voltage	250 VAC , 600 VAC/DC
Rated current	10A (VDE), 20A (UL/CSA)
Rated Power Acceptance IEC	4W / 10A @ Ta 23°C
	Admissible power acceptance at higher
	ambient temperature see derating cur-
	ves
Degree of Protection	IP40
Protection Class	Suitable for appliances with protection
	class I acc. to IEC 61140
Admissible Ambient Air Temp.	-40 °C to 85 °C
Climatic Category	40/085/21 acc. to IEC 60068-1
Material: Socket	Thermoplastic, black, UL 94V-0
Material: Terminals	Copper alloy, tin-plated
Unit Weight	5.5 g / 3.22 g
Storage Conditions	0°C to 60°C, max. 70% r.h.
Product Marking	5, Type, Rated Voltage, Rated current,
	Certification marks

Soldering Methods	Iron
	Soldering Profile
Solderability	350°C / 2 - 3 sec acc. to IEC 60068-2-
	20, Test Ta, method 2
Resistance to Soldering Heat	350°C / 10 sec acc. to IEC 60068-2-20,
	Test Tb, method 2
Contact Resistance	≤ 10 mΩ at 100 mA acc. to IEC
	60127-6
Dielectric Strength	> 3kV
	> 4 kV between L/N-PE
	(50 Hz: 1 min)
Impulse Withstand Voltage	> 4 kV between L-N
	> 6 kV between Front Panel and L/N
Insulation Resistance	$> 10 \text{M}\Omega$ between L-N
	$> 100\text{M}\Omega$ between Front Panel and L/N
	(500 VDC: 1 min)
Overvoltage Category	III acc. to IEC 60664-1
Pollution Degree	3 acc. to IEC 60664-1
Admissible Torque on Fixing	max 1.2 Nm
Nut	
Panel Thickness	max 7 mm

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about **Approvals**

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: FEU

Approval Logo	Certificates	Certification Body	Description
_DVE	VDE Approvals	VDE	VDE Certificate Number: 40045912
c FU °us	UL Approvals	UL	UR File Number: E39328

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
<u>IEC</u>	Designed according to	IEC 60127-6	Miniature fuses. Part 6. Fuse-holders for miniature fuse-links
(UL)	Designed according to	UL 4248-1	Standard for Safety Fuseholders
GFA Group	Designed according to	CSA C22.2 no. 4248.1	Industrial Control Equipment

Application standards

Application standards where the product can be used


Organization	Design	Standard	Description
<u>IEC</u>	Suitable for applications acc.	IEC/UL 62368-1	Audio/video, information and communication technology equipment - Part 1: Safety requirements
<u>IEC</u>	Suitable for applications acc.	IEC 60335-1	Safety of electrical appliances for household and similar purposes. Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 & -13.


Compliances

The product complies with following Guide Lines


	9		
Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
UK CA	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
RoHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
©	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.
00	White Paper Glow wire test	SCHURTER AG	Meets the requirements of IEC 60335-1 for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 &-13.


Dimension [mm] 46.5 mm






Variant 0031.1653 Variant 0031.1673






Variant 0031.1693

Variant 0031.1694



Mounting holes

Derating Curves



Ambient Air Temperature Ta $^{\circ}\text{C}$

All Variants

Holder	Cap	Fuse-Link	Terminal	Position End-Terminal	Degree of Protection	Colour Cap	Remark	Order Number	_
•	-	5 x 20 / 6.3 x 32mm	Quick-Connect 4.8 x 0.5	90° to Fuse Axis	IP40	-	-	0031.1693	
•	-	5 x 20 / 6.3 x 32mm	Quick-Connect 4.8 x 0.5	Straight to Fuse Axis	IP40	-	-	0031.1694	
•	-	5 x 20 / 6.3 x 32mm	Solder	90° to Fuse Axis	IP40	-	-	0031.1653	
•	-	5 x 20 / 6.3 x 32mm	Solder	90° to Fuse Axis	IP40	-	See details in drawing	0031.1673	
•	slotted	5 x 20mm	Quick-Connect 4.8 x 0.5	90° to Fuse Axis	IP40	-	0031.1693 + 0031.1663	0031.1706	
•	slotted	6.3 x 32mm	Solder	90° to Fuse Axis	IP40	-	0031.1673 + 0031.1661	0031.1672	
•	slotted	5 x 20mm	Solder	90° to Fuse Axis	IP40	-	0031.1673 + 0031.1663	0031.1753	
•	Fingergrip	6.3 x 32mm	Solder	90° to Fuse Axis	IP40	-	0031.1673 + 0031.1667	0031.1755	

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Packaging Unit

Bulk (100 pcs.)

Required Accessory

Description



Fingergrip_FEU__FAU__FAC
Caps Fingergrip for Holder FEU, FAU, FAC



Caps_to_FEU__FAU__FAC Caps to Holder FEU, FEU (Med), FAU, FAC

Accessories



Nut_for_fuse_holder Mounting accessories for fuse holder



Designation_plates_for_fuse_holders Marking plate for Fuseholders