

## Angular milling cutter 90°

For indexable milling insert WNEU 0403.

**ATORN®**

### Application

Powerful angular milling cutter with particularly economic, double-sided reversible tip with 6 cutting edges. Flexible use for multiple machining steps, such as face, angular, trim and groove milling.

### Version

- Wear-resistant, nickel-plated version
- Internal cooling

### Advantage

- 6 cutting edges on double-sided indexable insert
- special chip breaker geometry enables low power consumption
- Large plate thickness for optimum process reliability
- Optimised plane cutting edge for high surface quality



<b>Art. No.</b>	<b>16020 850</b>
<b>Cutting edge diameter</b>	50 mm
<b>Length</b>	50 mm
<b>Bore diameter</b>	22 mm
<b>max. ap</b>	3.5 mm
<b>Number of cutting edges</b>	8 PCS

### EAN-Code

4050293534870