

Combination spanner (DIN 3113 B)

DIN 3113 B, jaw angle 15°, ring side flat with depressed centre

ATORN[®]



Version

- With completely new special surface
- Maximum resistance against contact corrosion
- 15x greater corrosion protection against exposure to temperature, road salt and environmental influences compared to conventionally coated keys
- Up to 720 hours in the salt spray test in accordance with DIN EN ISO 9227
- Environmentally friendly chromium-VI-free coating process
- Made from chromium-vanadium steel, die-forged and hardened.
- DIN 3113 B

Advantage

- Extremely durable and robust industrial design

Art. No.	52039 108
Width across flats	8 mm
Length	125 mm
Tip profile type	ENERGY profile
Jaw position	15 Degree
Surface	Special coating according to specifications
Material	Chrome-vanadium steel
DIN	3113

EAN-Code

4050293537208