

Pneumatic two-hand grinder SBRH 8-12/2

With lever valve



Application:

For extreme brushing, grinding and milling work.

Execution:

- Rear air exhaust
- Paired bearing

Advantage:

- Optimal guidance due to extended shape and particularly stable bearing

Delivery:

Includes collet chuck ZG 7/6 mm and collet chuck key size 11 + 14; in box



Art. no.	75036 210
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150020770
Model	SBRH 8-12/2
Valve design	Lever valve
Motor design	Vane motor
Max. idle speed	12000 rpm
Power output	400 W
Air consumption	850 l/min
Length	300 mm
Diameter of housing	41 mm
Max. clamping diameter	8 mm
Collet chuck diameter	6 mm
Max. HM rotating milling cutter diameter	15 mm
Weight	1.268 kg
Made in	Germany
Compatible with	Hose unit 001366580
Gross Weight	1.700 kg
Product Group	748