

**Testing tools  
MULTIMETER 1037**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Multimeters are capable of measuring a number of variables. Each instrument can measure voltage and resistance, as well as performing continuity and diode testing as standard.

In addition, the individual multimeters also feature extra measuring options such as current, frequency, capacitance and temperature. Digital multimeters have the advantage of a clear display which can be read easily and directly. With these instruments, mistakes arising from faulty conversion of the measuring ranges or misreading the display are a thing of the past.

**General ordering data**

Type	MULTIMETER 1037
Order No.	<a href="#">9423580000</a>
Version	Multimeter
GTIN (EAN)	4032248406142
Qty.	1 pc(s).

**Testing tools  
MULTIMETER 1037**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	214.5 mm	Width (inches)	8.445 inch
Height	44 mm	Height (inches)	1.732 inch
Depth	66 mm	Depth (inches)	2.598 inch
Weight	258 g	Net weight	914 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Technical data**

Version Multimeter + clamp-on meter

**Measuring and testing devices**

AC voltage measuring range	0.2 - 750 V	Battery type	9V block battery
DC voltage measuring range	0,2 - 1000 V	Display	digital
Frequency measurement	No	Frequency range, max.	500 Hz
Frequency range, min.	50 Hz	Measured capacitance value, max.	200 µF
Measured current value, max.	200 A	Measuring range category	CAT III
Opening width of current-measuring clamp-on attachment	23 mm	Resistance measuring range, max.	200 kΩ
Resistance measuring range, min.	0.2 Ω	Selection of measuring range	Manual
Test probe	Yes	Tested and approved according to	EN/IEC 61010-1
Working temperature, max.	50 °C	Working temperature, min.	0 °C

**Classifications**

ETIM 3.0	EC000069	ETIM 4.0	EC000069
ETIM 5.0	EC000069	ETIM 6.0	EC000069
UNSPSC	41-11-36-37	eClass 5.1	27-20-03-01
eClass 6.2	27-20-03-01	eClass 7.1	27-20-03-01
eClass 8.1	27-20-03-01	eClass 9.0	27-20-03-01
eClass 9.1	27-20-03-08		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)

**Data sheet**

**Testing tools**  
**MULTIMETER 1037**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Example of use**

