

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2138141104](#)
Status: **Active**
Overview: [Mega-Fit Power Connectors](#)
Description: Mega-Fit Plug Housing, Single Row, 4 Circuit, UL 94V-0, Glow-Wire Capable, Panel Mount

Documents:

| | |
|--|---|
| Drawing (PDF) | Packaging Specification 2138140001-PK-000 (PDF) |
| Product Specification 1054171000-PS-000 (PDF) | Datasheet (PDF) |
| Application Specification 768232000-AS-000 (PDF) | RoHS Certificate of Compliance (PDF) |

General

| | |
|----------------|---|
| Product Family | Crimp Housings |
| Series | 213814 |
| Application | Power, Wire-to-Wire |
| Overview | Mega-Fit Power Connectors |
| Product Name | Mega-Fit |
| UPC | 193264466061 |

Physical

| | |
|-------------------------------|--------------------------------|
| Circuits (maximum) | 4 |
| Color - Resin | Black |
| Gender | Plug |
| Glow-Wire Capable | Yes |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 3.350/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | Yes |
| Pitch - Mating Interface | 5.70mm |
| Pitch - Termination Interface | 5.70mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C, -40° to +120°C |

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|-------------------|
| Application Specification | 768232000-AS-000 |
| Packaging Specification | 2138140001-PK-000 |
| Product Specification | 1054171000-PS-000 |
| Sales Drawing | 2138140001-SD-000 |



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[213814 Series](#)

Mates With

Mega-Fit Receptacle Housing [200456](#)

Use With

Mega-Fit TPA [105415](#)
Mega-Fit Crimp
Terminals [105417](#) , [105418](#)