


## Cabinet workbench series V 1500 with lowerable transport wheels

Zinc sheet coating 1500 mm, 4 drawers with full extension, 1 door, lever-operated wheels



### Execution:

- Solidly welded steel sheet construction
- Base made of square-section steel tube 45 x 45 x 2 mm, with level compensation
- 4 drawers with 100% full extension on the left, 2 x front height 90 mm, 2 x front height 180 mm, 1 door, height 540 mm on the right



<b>Art. no.</b>	<b>50201 535</b>
<b>Brand</b>	ANKE
<b>Manufacturer Part Number</b>	999.001.1200
<b>Working height</b>	850 mm
<b>Worktop width</b>	1500 mm
<b>Number of drawers</b>	4 PCS
<b>Worktop height</b>	50 mm
<b>Number of doors</b>	1 PCS
<b>Worktop depth</b>	700 mm
<b>Pullout type</b>	Full extension
<b>On castors</b>	Yes
<b>Colour of front</b>	Gentian blue RAL 5010
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Drawer surface</b>	0.27 m <sup>2</sup>
<b>With single pull-out safety brake</b>	Yes
<b>Surface</b>	Powder-coated
<b>Load-carrying capacity</b>	450 kg
<b>Levelling</b>	Yes
<b>Lock type</b>	DOM® locking system
<b>Material of worktop</b>	Zinc sheet covering
<b>Drawer front height</b>	2 x 90 mm, 2 x 180 mm
<b>Drawer width (inner dimension)</b>	500 mm
<b>Drawer width (inner dimension) x drawer depth (inner dimension)</b>	500 x 540 mm
<b>Drawer depth (inner dimension)</b>	540 mm
<b>Load-carrying capacity per drawer</b>	100 kg
<b>Central locking</b>	Yes
<b>Gross Weight</b>	167.414 kg
<b>Product Group</b>	502

### EAN

4014641070670