



Actinic BL PL-S/PL-L

Insect PL-L 36W /10

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Mechanical and Housing	
Cap-Base	2G11 [2G11]	Bulb Shape	2xT16
Light Technical		Approval and Application	
Color Code	210 [leadfree 360 glass (10)]	Mercury (Hg) Content (Max)	2.1 mg
Chromaticity Coordinate X (Nom)	220	Mercury (Hg) Content (Nom)	2.0 mg
Chromaticity Coordinate Y (Nom)	215		
Operating and Electrical		Product Data	
Power Consumption	36 W	Full product code	871150026481740
Lamp Current (Nom)	0.435 A	Order product name	Insect PL-L 36W /10
Voltage (Nom)	106 V	Order code	927903421007
Voltage (Nom)	106 V	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	25
		Material number (12NC)	927903421007
		Full product name	Insect PL-L 36W /10

Actinic BL PL-S/PL-L

EAN/UPC - Case


8711500264824

Dimensional drawing



Product	D1 (max)	D (max)	C1	A (max)	B (max)	C (max)
Insect PL-L 36W /10	18 mm	39 mm	20.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data



Spectral Power Distribution Colour - Insect PL-L 36W /10

