



## Impact Pin Moisture Probe

### P/N: MR05

#### Revision

26727

#### Last modified

2015-06-12 10:27 UTC+1

#### Copyright

© 2018, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

#### Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to [exportquestions@flir.com](mailto:exportquestions@flir.com) with any questions.

#### Website

<http://www.flir.com>

#### Customer support

<http://support.flir.com>



Part number	MR05
Part description	Impact Pin Moisture Probe
The FLIR MR05 upgrades your FLIR moisture meter to help you easily test for moisture in challenging spots—on rough or uneven surfaces, in corners, in hard woods or high-density materials, and even, with ease, in areas without a dry reference. Made with extra-durable pins and a metallic impact plate that can withstand hammering to drive pins into the hardest materials, the FLIR MR05 lets you tackle the toughest moisture-measurement challenges all day long. Key features include six additional sets of thick and thin pins, an external pin accessory for the FLIR moisture meter mount for extended reach, a 1/4"-20 integrated wrench on the cap to replace pins, a durable BNC connector, a 2 m coiled cord, and a 2 year warranty.	

<b>Meter data</b>	
Suitable main unit	MR77 (MR160 and MR176 coming soon)
Cable length	2.45 m (8') uncoiled
Pin length	10 mm (0.4")
Warranty	2 years (with registration)

<b>Meter physical data</b>	
Weight	195 g (0.43 lb)
Dimensions (H × W × L)	8.4 cm × 7.1 cm × 3.8 cm (3.3" × 2.8" × 1.5")
Material	PC-ABS
Color	Black

<b>Shipping information</b>	
Packaging type	Color retail packaging
Packaging contents	MR05, manual, six extra pin sets (three wide, three standard)
Packaging weight	0.4 kg (0.8 lb)
Packaging dimensions (H × W × L)	31.1 cm × 15.2 cm × 5.7 cm (12.25 × 6 × 2.2 in)
Inner shipping carton weight	1.8 kg (3.98 lb)
Inner shipping carton dimensions (H × W × L)	58.5 cm × 15.9 cm × 12.7 cm (23" × 7" × 5")
Inner shipping carton quantity	4
Master carton weight	6 kg (13.2 lb)
Master carton dimensions (H × W × L)	60.9 cm × 39.4 cm × 17.8 cm (24" × 16" × 7")