


# 229/230 Series 2AG, Slo-Blo® Fuse with Indicating Option





#### **Agency Approvals**

Agency	Agency File Number	Ampere Range		
(jr	E10480	250mA - 3.5A		
<b>(P</b> )	LR 29862	250mA - 7A		
<b>71</b> °	E10480	4A - 7A		
PS E	NBK200405 - E10480C/D NBK110512 - E10480A/B NBK210405 - E10480E/F	1A - 3.5A 4A - 5A 6A - 7A		
Œ		250mA - 7A		

#### **Electrical Characteristics for Series**

% of Ampere Rating	Opening Time		
100%	4 hours, Minimum		
135%	1 hour, Maximum		
200%	3 seconds, Minimum		
200 %	20 seconds, Maximum		

#### **Description**

Littelfuse 229/230 series Slo-Blo® Fuses are available in 2AG size cartridge or axial lead form, offer tripped fuse indicating option, and offer features designed to meet rigorous Telecom industry requirements.

229/230 series product ordered with the tripped fuse indicating option show discoloration of the glass body immediately after trip. They offer the same performance characteristics as standard product, and help to reduce time locating the tripped fuse and troubleshooting circuit issues.

The 229/230 series 0.25A - 1.25A range combines conventional overcurrent protection with ability to withstand high current, short duration pulses which complies to short circuit requirements of UL 1459 for telephone equipment. Insulating sleeve option is also available. Please refer to the Surge Withstand Specifications section of this document for additional information.

#### **Features**

- Available in cartridge and axial lead form, and a wide range of lead forming dimension and packaging options
- In accordance with UL Standard 248-14
- RoHS compliant and Lead-free
- Tripped fuse indicating option (add suffix 'S' to part number)
- Fuses are available for board washable with the additional sealing process (add suffix 'A' to part number)
- Sleeved fuse option available (contact Littelfuse for additional information)

#### **Additional Information**



Datasheet 229 Series



Datasheet 230 Series



Resources 229 Series



Resources 230 Series



Samples 229 Series



Samples 230 Series

# Axial Lead & Cartridge Fuses 2AG > Time Lag > 229/230 Series

#### **Electrical Characteristic Specification by Item**

	Ampere Voltage Nominal Cold		Nominal	Agency Approvals						
Amp Code	Rating (A)	Rating (V)	Interrupting Rating	Resistance (Ohms)	Melting I²t (A² sec)	(I)	<i>91</i>	PS	<b>(</b>	Œ
.250	0.25	250		2.4300	0.216	X			Х	Х
.350	0.35	250		1.3100	0.490	Х			Х	Х
.375	0.375	250	35A@250Vac	1.1685	0.580	X			Х	Х
.500	0.5	250	10KA@125Vac	0.6935	1.16	X			Х	Х
.600	0.6	250	10KA@125Vdc 80A@310Vac	0.4805	1.75	X			Х	Х
.750	0.75	250	80A@310VaC	0.3430	2.95	X			Х	Х
.800	0.8	250		0.3060	3.45	X			Х	Х
001.	1	250		0.2120	5.64	X		Х	Х	Х
1.25	1.25	250		0.1460	9.80	X		Х	Х	Х
01.5	1.5	250	100A@250Vac	0.1077	15.0	X		X	Х	Х
002.	2	250	10KA@125Vac	0.0698	30.0	X		Х	Х	Х
2.25	2.25	250	10KA@125Vdc 80A@310Vac	0.0567	39.0	X		X	Х	Х
02.5	2.5	250	80A@310VaC	0.0502	50.0	X		X	Х	Х
003.	3	250		0.0383	77.0	Х		Х	Х	Х
03.5	3.5	250	100A@250Vac 10KA@125Vac 10KA@125Vdc	0.0312	110.0	X		X	х	х
004.	4	125		0.0258	148.0		Х	Х	Х	Х
005.	5	125	400A@125Vac 400A@125Vdc	0.0186	267		Х	Х	Х	Х
006.	6	125		0.0141	380		Х	Х	X	Х
007.	7	125		0.0116	464		Х	Х	Х	Х

#### **Surge Withstand Specifications**


**Peak Withstand Current(Ip):** These fuses will withstand 50 repetitions of a double exponential impulse wave having peak currents(Ip) and peak voltages as listed.

Amp Code	Ampere Rating (A)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I²t (A² sec)	10×160 µs 1500V	10×560 μs 800V	10×1000 μs 1000V
.250	0.25		2.4300	0.216	23.0A	16.6A	12.4A
.350	0.35		1.3100	0.490	34.0A	25.8A	19.3A
.375	0.375	60A@600Vac	1.1685	0.580	40.0A	25.4A	19.0A
.500	0.5		0.6935	1.16	60.0A	37.7A	28.2A
.600	0.6	40A@600Vac 7A@600Vac	0.4805	1.75	71.0A	47.2A	35.3A
.750	0.75	2.2A@600Vac	0.3430	2.95	91.0A	65.5A	49.0A
.800	0.8	2.2/18/00/00	0.3060	3.45	104.0A	68.9A	51.6A
001.	1		0.2120	5.64	130A	88.6A	66.3A
1.25	1.25*		0.1460	9.80	162.0A	118.1A	100.0A


<sup>\* 500</sup>A peak, 2500V, 2×10 microseconds, 20 repetitions




#### **Temperature Rerating Curve**



#### **Average Time Current Curves**



#### **Soldering Parameters - Wave Soldering**



#### **Recommended Process Parameters:**

Wave Parameter	Lead-Free Recommendation			
Preheat:				
(Depends on Flux Activation Temperature)	(Typical Industry Recommendation)			
Temperature Minimum:	100° C			
Temperature Maximum:	150° C			
Preheat Time:	60-180 seconds			
Solder Pot Temperature:	260° C Maximum			
Solder DwellTime:	2-5 seconds			

#### **Recommended Hand-Solder Parameters:**

Solder Iron Temperature: 350° C +/- 5°C

Heating Time: 5 seconds max.

Note: These devices are not recommended for IR or Convection Reflow process.

# Axial Lead & Cartridge Fuses

2AG > Time Lag > 229/230 Series

#### **Product Characteristics**


Materials	Body: Glass Cap: Nickel-plated brass Leads: Tin-plated Copper			
Terminal Strength	MIL-STD-202G, Method 211A, Test Condition A			
Solderability	Reference IEC 60127 Second Edition 2003-01 Annex A			
Product Marking	Cap1: Cap2:	Brand logo, current and voltage ratings Series and agency approval marks		

Operating Temperature	-55°C to +125°C			
Thermal Shock	MIL-STD-202G, Method 107G, Test Condition B: (5 cycles - -65°C to 125°C)			
Vibration	MILSTD-202G, Method 201A			
Humidity	MIL-STD-202G, Method 103B, Test Condition A: High RH (95%) and Elevated temperature (40°C) for 240 hours			
Salt Spray	MIL-STD-202G, Method 101D, Test Condition B			

#### **Dimensions**

## **229** 000P Series

### 230 000P Series



Axial Lead Material: Solder coated Copper.

#### **Part Numbering System**

