


4.0x4.0mm RIGHT ANGLE SURFACE MOUNT **LED LAMP**



Part Number: KA-4040QBS-G Blue

Features

- Single color.
- Suitable for all SMT assembly and solder process.
- Available on tape and reel.
- Ideal for backlighting.
- Package: 500pcs / reel.
- Moisture sensitivity level : level 3.
- · RoHS compliant.

Description


The Blue source color devices are made with InGaN Light Emitting Diode.

Static electricity and surge damage the LEDS.


It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs.

All devices, equipment and machinery must be electrically grounded.

Package Dimensions








- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.25(0.01") unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
 The device has a single mounting surface. The device must be mounted according to the specifications.

SPEC NO: DSAK9839 **REV NO: V.5B** DATE: MAR/25/2013 PAGE: 1 OF 6 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1201007055

Handling Precautions

Compare to epoxy encapsulant that is hard and brittle, silicone is softer and flexible. Although its characteristic significantly reduces thermal stress, it is more susceptible to damage by external mechanical force. As a result, special handling precautions need to be observed during assembly using silicone encapsulated LED products. Failure to comply might lead to damage and premature failure of the LED.

1. Handle the component along the side surfaces by using forceps or appropriate tools.



2. Do not directly touch or handle the silicone lens surface. It may damage the internal circuitry.





3. As silicone encapsulation is permeable to gases, some corrosive substances such as H_2S might corrode silver plating of leadframe. Special care should be taken if an LED with silicone encapsulation is to be used near such substances.

Detailed application notes are listed on our website. http://www.kingbright.com/application notes

SPEC NO: DSAK9839 REV NO: V.5B DATE: MAR/25/2013 PAGE: 2 OF 6

APPROVED: WYNEC CHECKED: Allen Liu DRAWN: Y.Liu ERP: 1201007055

Selection Guide

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
		2.	Min.	Тур.	201/2
KA-4040QBS-G	Blue (InGaN)	Water Clear	200	350	120°

Notes:

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value. 2. Luminous intensity/ luminous Flux: +/-15%.
- 3.Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Blue	461		nm	IF=20mA
λD [1]	Dominant Wavelength	Blue	465		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Blue	25		nm	IF=20mA
С	Capacitance	Blue	100		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Blue	3.3	4	V	IF=20mA
lR	Reverse Current	Blue		50	uA	V _R =5V

Notes:


- 1.Wavelength: +/-1nm. 2. Forward Voltage: +/-0.1V.
- 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.


Absolute Maximum Ratings at TA=25°C


A too o to					
Parameter	Blue				
Power dissipation	120	mW			
DC Forward Current	30	mA			
Peak Forward Current [1]	150	mA			
Reverse Voltage	5	V			
Operating Temperature	-40°C To +85°C				
Storage Temperature	-40°C To +85°C				


Note: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.


SPEC NO: DSAK9839 **REV NO: V.5B** DATE: MAR/25/2013 PAGE: 3 OF 6 **APPROVED: WYNEC CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1201007055















SPATIAL DISTRIBUTION

SPEC NO: DSAK9839 REV NO: V.5B DATE: MAR/25/2013 PAGE: 4 OF 6
APPROVED: WYNEC CHECKED: Allen Liu DRAWN: Y.Liu ERP: 1201007055

KA-4040QBS-G

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




NOTES:

1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.

2.Don't cause stress to the epoxy resin while it is exposed to high temperature.


3.Number of reflow process shall be 2 times or less.


Recommended Soldering Pattern (Units: mm; Tolerance: ± 0.1)




Tape Dimensions (Units: mm)

Reel Dimension





SPEC NO: DSAK9839 **REV NO: V.5B DATE: MAR/25/2013** PAGE: 5 OF 6 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1201007055





SPEC NO: DSAK9839 APPROVED: WYNEC REV NO: V.5B CHECKED: Allen Liu DATE: MAR/25/2013 DRAWN: Y.Liu PAGE: 6 OF 6 ERP: 1201007055