


Terminal Protection to IP20

Dims: to DIN 43880 W. 17.5mm



- *NEW* 17.5mm DIN rail housing
- □ Instantaneous Contact (Relay 1)
 - Delay On Operate timing function (Relay 2)
- 7 Selectable time ranges (0.1 seconds 100 hours)
- Fine adjustment of selected time range
- Multi-voltage input (12 230V AC/DC)
- 2 x SPDT relay output 8A
- Green LED indication for supply / timing status
- Red LED indication for relay statuses
- Conforms to IEC 61812





INSTALLATION AND SETTING

- BEFORE INSTALLATION, ISOLATE THE SUPPLY.
- Connect the unit as required.

Setting the unit

Set the "Range" to the required position (depending on whether seconds, minutes or hours are required), then set the "Set %" adjustment so required. The "Set %" is a % of the selected range, so 60% of the 1 – 10 hour range will give 6 hours.

Applying power

- Apply power and the green LED will start flashing to indicate timing is in progress. Contacts 15 and 18 will close as soon as power is applied (Instantaneous Relay RLY1) and the red relay LED
 will illuminate. Contacts 25 and 26 (Timed Relay RLY2) will remain closed during this period
- At the end of the delay period "t" contacts 25 and 26 will open 25 and 28 will close. The red relay LED @ will illuminate.
- Both relays will remain in the energised state until power is removed. Re-applying power will
 repeat the whole process again.

Note:

¹ In accordance with IEC 61812, the green LED is permitted to extinguish during a voltage dip or momentary interruption of the power supply providing the state of the output relay does not change.


interruption of the power supply providing the state of the output relay does not change.


² The dip / interruption (reset) duration and levels are defined in the product standard however, the standard allows for these to be different from the levels actually specified.

TECHNICAL SPECIFICATION Supply voltage U (A1, A2): 12 - 230V AC/DC 48 - 63Hz (AC supplies) Frequency range Supply variation AC: +15/-10% DC: +/-15% III (IEC 60664) Overvoltage category: Rated impulse withstand voltage 4kV (1.2/50μS) IEC 60664 Power consumption (max.): 12V 24V 110V 230V 0.8VA 0.6VA 2.6VA 6.8VA 0.52W Timing function (RLY1): Instantaneous Contact Time delay: <100mS (to relay energising) Timing function (RLY2): Delay On Operate Timing ranges (7): Minutes Hours: Seconds: 0.1 - 10.1 - 10.1 - 11 – 10 1 - 101 – 10 10 - 100 Reset time²: <100mS ± 1% of maximum full scale Accuracy Adjustment accuracy < 5% of maximum full scale Repeat accuracy: \pm 0.5% at constant conditions (IEC 61812) Drift with temperature: ±0.05% / °C ±0.2%/V Drift with voltage: Power on indication / Timing¹: Green LED Relay status (Instantaneous - RLY1) Red LED Relay status (Delay On Op. - RLY2) Red LED Ambient temp: -20 to +60°C Relative humidity +95% Output (15, 16, 18 / 25, 26, 28): SPDT relay (x2) AC1 250V 8A (2000VA) 250V 5A (no), 3A (nc) AC15 25V 8A (200W) DC1 Electrical life: ≥ 150,000 ops at rated load Dielectric voltage 2kV AC (rms) IEC 60947-1 4kV (1.2/50μS) IEC 60664 Rated impulse withstand voltage Housing Orange flame retardant UL94 ≈ 80g Weight: On to 35mm symmetric DIN rail to BS EN 60715 Mounting option or direct surface mounting via 2 x M3.5 or 4BA screws using the black clips provided on the rear of the unit. Terminal conductor size ≤ 2 x 2.5mm² solid or stranded Conforms to IEC 61812 Approvals CUL US LISTED IND. CONT. EQ. CE, C-tick Cand RoHS Compliant. EMC: Immunity: EN 61000-6-2 (EN 61000-4-3 10V/m

80MHz - 2.7GHz)

Emissions: EN 61000-6-4





Installation work must be carried

out by qualified personnel.

