

## SAFETY DATA SHEET

JENOLITE DIRECT TO METAL SATIN SAGE GREEN 7494C - 89456 & 89656



Page: 1

Compilation date: 24/06/2021

Revision date: 20/09/2018

Revision No: 1

### Section 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

**Product name:** JENOLITE DIRECT TO METAL SATIN SAGE GREEN 7494C

**Product code:** 89456 & 89656

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### 1.3. Details of the supplier of the safety data sheet

**Company name:** Jenolite UK Ltd

Unit 1

Albone way

Biggleswade

Bedfordshire

SG18 8BN

England

**Tel:** 01234 924 794

**Email:** Sales@jenolite.com

#### 1.4. Emergency telephone number

**Emergency tel:** 01234 924 794

### Section 2: Hazards identification

#### 2.1. Classification of the substance or mixture

**Classification under CLP:** Skin Sens. 1A: H317; Aquatic Chronic 3: H412; Eye Irrit. 2: H319; Flam. Aerosol 1: H222; STOT SE 3: H336; -: EUH066; -: H229

**Most important adverse effects:** Repeated exposure may cause skin dryness or cracking. Extremely flammable aerosol. Pressurised container: May burst if heated. May cause an allergic skin reaction. Causes serious eye irritation. May cause drowsiness or dizziness. Harmful to aquatic life with long lasting effects.

#### 2.2. Label elements

##### Label elements:

**Hazard statements:** EUH066: Repeated exposure may cause skin dryness or cracking.

H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H412: Harmful to aquatic life with long lasting effects.

[cont...]

# SAFETY DATA SHEET

JENOLITE DIRECT TO METAL SATIN SAGE GREEN 7494C NPD10738

Page: 2

**Hazard pictograms:** GHS02: Flame

GHS07: Exclamation mark



**Signal words:** Danger

**Precautionary statements:** P102: Keep out of reach of children.

P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P211: Do not spray on an open flame or other ignition source.

P251: Do not pierce or burn, even after use.

P362+P364: Take off contaminated clothing and wash it before reuse.

P410+P412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

## 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

ACETONE - REACH registered number(s): 01-2119471330-XXXX

EINECS	CAS	PBT / WEL	CLP Classification	Percent
200-662-2	67-64-1	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	30-50%

PETROLEUM GASES, LIQUEFIED

270-704-2	68476-85-7	Substance with a Community workplace exposure limit.	Flam. Gas 1: H220; Press. Gas: H280	30-50%
-----------	------------	--	-------------------------------------	--------

HYDROCARBONS, C9-12, N-ALKANES, ISOALKANES, CYCLICS, (2-25%) AROMATICS - REACH registered number (s): 01-2119458049-33

919-446-0	-	-	Flam. Liq. 3: H226; STOT SE 3: H336; Asp. Tox. 1: H304; Aquatic Chronic 2: H411; -: EUH066	1-10%
-----------	---	---	--	-------

D40 NAPHTHA (PETROLEUM), HYDROTREATED HEAVY, DE-AROMATISED - REACH registered number(s): 01-2119463258-33-XXXX

919-857-5	64742-48-9	-	Flam. Liq. 3: H226; STOT SE 3: H336; Asp. Tox. 1: H304; -: EUH066	1-10%
-----------	------------	---	--	-------

[cont...]

## SAFETY DATA SHEET

JENOLITE DIRECT TO METAL SATIN SAGE GREEN 7494C NPD10738

Page: 3

### HYDROCARBONS, C9, AROMATICS

918-668-5	-	-	Flam. Liq. 3: H226; Asp. Tox. 1: H304; Aquatic Chronic 2: H411; STOT SE 3: H335; STOT SE 3: H336	1-10%
-----------	---	---	--	-------

### DIPENTENE

205-341-0	138-86-3	-	Flam. Liq. 3: H226; Skin Irrit. 2: H315; Skin Sens. 1: H317; Aquatic Acute 1: H400; Aquatic Chronic 1: H410	<1%
-----------	----------	---	---	-----

### 2-BUTANONE OXIME

202-496-6	96-29-7	-	Carc. 2: H351; Acute Tox. 4: H312; Eye Dam. 1: H318; Skin Sens. 1: H317	<1%
-----------	---------	---	---	-----

### COBALT BIS(2-ETHYLHEXANOATE)

205-250-6	136-52-7	-	Eye Irrit. 2: H319; Skin Sens. 1A: H317; Repr. 2: H361; Aquatic Acute 1: H400; Aquatic Chronic 3: H412; Repr. 1A: H360	<1%
-----------	----------	---	--	-----

### 2-ETHYLHEXANOIC ACID, ZIRCONIUM SALT

245-018-1	22464-99-9	-	Repr. 2: H361d	<1%
-----------	------------	---	----------------	-----

### PHTHALIC ANHYDRIDE

201-607-5	85-44-9	-	Acute Tox. 4: H302; STOT SE 3: H335; Skin Irrit. 2: H315; Eye Dam. 1: H318; Resp. Sens. 1: H334; Skin Sens. 1: H317	<1%
-----------	---------	---	---	-----

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor. Move the exposed person to fresh air.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

[cont...]

## SAFETY DATA SHEET

JENOLITE DIRECT TO METAL SATIN SAGE GREEN 7494C NPD10738

Page: 4

### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Eye bathing equipment should be available on the premises.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed.

**Suitable packaging:** Must only be kept in original packaging.

### 7.3. Specific end use(s)

**Specific end use(s):** No data available.

[cont...]

## SAFETY DATA SHEET

JENOLITE DIRECT TO METAL SATIN SAGE GREEN 7494C NPD10738

Page: 5

### Section 8: Exposure controls/personal protection

#### 8.1. Control parameters

**Hazardous ingredients:**

**ACETONE**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	500ppm 1210mg/m <sup>3</sup>	1500ppm 3620mg/m <sup>3</sup>	-	-

**PETROLEUM GASES, LIQUEFIED**

UK	1,750mg/m <sup>3</sup>	2,180mg/m <sup>3</sup>	-	-
----	------------------------	------------------------	---	---

**D40 NAPHTHA (PETROLEUM), HYDROTREATED HEAVY, DE-AROMATISED**

UK	150ppm 1000mg/m <sup>3</sup>	-	-	-
----	------------------------------	---	---	---

**HYDROCARBONS, C9, AROMATICS**

EU	Shellsol A	-	100 mg/ml <sup>3</sup>	-
----	------------	---	------------------------	---

**PHTHALIC ANHYDRIDE**

UK	4 mg/m <sup>3</sup>	12 mg/m <sup>3</sup>	-	-
----	---------------------	----------------------	---	---

#### DNEL/PNEC Values

**Hazardous ingredients:**

**ACETONE**

Type	Exposure	Value	Population	Effect
DNEL	Dermal	186mg/kg/day	Workers	Systemic
DNEL	Inhalation	2420mg/m <sup>3</sup>	Workers	Local
DNEL	Inhalation	1210mg/m <sup>3</sup>	Workers	Systemic
DNEL	Oral	62mg/kg/day	Consumers	Systemic
DNEL	Dermal	62mg/m <sup>3</sup>	Consumers	Systemic
DNEL	Inhalation	200mg/m <sup>3</sup>	Consumers	Systemic
PNEC	Fresh water	10.6mg/l	-	-
PNEC	Marine water	1.06mg/l	-	-
PNEC	Fresh water	Intermittent release	-	-
PNEC	Fresh water sediments	30.4 mg/kg	-	-
PNEC	Marine sediments	3.04mg/kg	-	-
PNEC	Soil (agricultural)	29.5mg/kg	-	-
PNEC	Microorganisms in sewage treatment	100mg/l	-	-

[cont...]

## SAFETY DATA SHEET

JENOLITE DIRECT TO METAL SATIN SAGE GREEN 7494C NPD10738

Page: 6

### D40 NAPHTHA (PETROLEUM), HYDROTREATED HEAVY, DE-AROMATISED

Type	Exposure	Value	Population	Effect
DNEL	Dermal	208mg/kg/day	Workers	Systemic
DNEL	Inhalation	871 mg/m <sup>3</sup>	Workers	Systemic
DNEL	Dermal	125mg/kg/day	Consumers	Systemic
DNEL	Inhalation	185mg/m <sup>3</sup>	Consumers	Systemic
DNEL	Oral	125mg/kg/day	Consumers	Systemic

#### 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area.

**Respiratory protection:** Self-contained breathing apparatus must be available in case of emergency.

**Hand protection:** Protective gloves. Chemically resistant gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

**Environmental:** Not applicable.

#### Section 9: Physical and chemical properties

##### 9.1. Information on basic physical and chemical properties

**State:** Aerosol

**Colour:** Green

**Odour:** Characteristic odour

**Flash point°C:** <23

##### 9.2. Other information

**Other information:** No data available.

#### Section 10: Stability and reactivity

##### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

##### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

##### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

##### 10.4. Conditions to avoid

**Conditions to avoid:** Heat.

##### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids.

[cont...]

# SAFETY DATA SHEET

JENOLITE DIRECT TO METAL SATIN SAGE GREEN 7494C NPD10738

Page: 7

## 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

#### Hazardous ingredients:

##### ACETONE

DERMAL	RAT	LD50	>7400	mg/kg
DERMAL	RBT	LD50	2000	mg/kg
ORAL	RAT	LD50	5800	mg/kg
VAPOURS	RAT	4H LC50	76000	mg/l

##### D40 NAPHTHA (PETROLEUM), HYDROTREATED HEAVY, DE-AROMATISED

DERMAL	RBT	LD50	>5000	mg/kg
GASES	RAT	4H LC50	>5000	mg/l
ORAL	RAT	LD50	>5000	mg/kg

##### DIPENTENE

IVN	MUS	LD50	1010	µl/kg
ORL	MUS	LD50	5550	µl/kg
ORL	RAT	LD50	5300	mg/kg

##### 2-BUTANONE OXIME

ORL	MUS	LD50	1	gm/kg
ORL	RAT	LD50	930	mg/kg
SCU	RAT	LD50	2702	mg/kg

##### PHTHALIC ANHYDRIDE

ORL	MUS	LD50	1500	mg/kg
ORL	RAT	LD50	1530	mg/kg

#### Relevant hazards for product:

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	-	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

[cont...]

## SAFETY DATA SHEET

JENOLITE DIRECT TO METAL SATIN SAGE GREEN 7494C NPD10738

Page: 8

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

**Other information:** Not applicable.

### Section 12: Ecological information

#### 12.1. Toxicity

**Hazardous ingredients:**

##### ACETONE

ALGAE	192H EC10	530	mg/l
Activated Sludge	30m EC10	1000	mg/l
DAPHNIA	48H EC50	8800	mg/l
Daphnia magna	192H EC10	2212	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	5540	mg/l

##### D40 NAPHTHA (PETROLEUM), HYDROTREATED HEAVY, DE-AROMATISED

ALGAE	72H IC50	>1000	mg/l
Daphnia magna	48H EC50	>1000	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	>1000	mg/l

##### HYDROCARBONS, C9, AROMATICS

ALGAE	72H IC50	2.9	mg/l
DAPHNIA	48H EC50	3.2	mg/l
FISH	96H LC50	9.2	mg/l

#### 12.2. Persistence and degradability

**Persistence and degradability:** Biodegradable.

#### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

#### 12.4. Mobility in soil

**Mobility:** Readily absorbed into soil.

#### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

#### 12.6. Other adverse effects

**Other adverse effects:** Negligible ecotoxicity.

[cont...]



# SAFETY DATA SHEET

JENOLITE DIRECT TO METAL SATIN SAGE GREEN 7494C NPD10738

Page: 9

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company. Dispose of contents and container according to national regulations.

**Recovery operations:** Not applicable.

**Disposal of packaging:** Not applicable.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

### 14.1. UN number

**UN number:** UN1950

### 14.2. UN proper shipping name

**Shipping name:** AEROSOLS

### 14.3. Transport hazard class(es)

**Transport class:** 2

### 14.4. Packing group

### 14.5. Environmental hazards

**Environmentally hazardous:** No

**Marine pollutant:** No

### 14.6. Special precautions for user

**Special precautions:** No special precautions.

**Tunnel code:** E

**Transport category:** 3

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Specific regulations:** Not applicable.

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

**Phrases used in s.2 and s.3:** EUH066: Repeated exposure may cause skin dryness or cracking.

H220: Extremely flammable gas.

[cont...]

## SAFETY DATA SHEET

JENOLITE DIRECT TO METAL SATIN SAGE GREEN 7494C NPD10738

Page: 10

H222: Extremely flammable aerosol.  
H225: Highly flammable liquid and vapour.  
H226: Flammable liquid and vapour.  
H229: Pressurised container: May burst if heated.  
H302: Harmful if swallowed.  
H304: May be fatal if swallowed and enters airways.  
H312: Harmful in contact with skin.  
H315: Causes skin irritation.  
H317: May cause an allergic skin reaction.  
H318: Causes serious eye damage.  
H319: Causes serious eye irritation.  
H334: May cause allergy or asthma symptoms or breathing difficulties if inhaled.  
H335: May cause respiratory irritation.  
H336: May cause drowsiness or dizziness.  
H351: Suspected of causing cancer.  
H360: May damage fertility or the unborn child.  
H361: Suspected of damaging fertility or the unborn child.  
H361d: Suspected of damaging the unborn child.  
H400: Very toxic to aquatic life.  
H410: Very toxic to aquatic life with long lasting effects.  
H411: Toxic to aquatic life with long lasting effects.  
H412: Harmful to aquatic life with long lasting effects.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product. Please note that due to the on-going change in regulation from CHIP to CLP, any MSDS information supplied by LMA is only considered accurate at the time of its creation. During this time classifications of substances may change. Therefore it is possible that can art work and MSDS information may differ. As such if you have any concerns we recommend you request a new MSDS from us every 6-12 months.