

Miniature cutting insert, type AF HW56 15

for axial recessing

ATORN[®]



Application

Sturdy geometry for axial recessing in the material groups of steel and (stainless steel) with low to high cutting speeds and medium cutting conditions.

Version

- solid carbide cutting insert with inner cooling

Advantage

- very hard cemented carbide type ensures low wear
- sturdy geometry for axial cutter insert
- extremely sharp cutting edges ensure cutting with process reliability

Art. no.	17132 212
ISO name	AF
Shaft diameter	4 mm
Length	51 mm
Clearance length	15 mm
Recessing width	1.5 mm
Plunge depth	2.8 mm
Programming size	1.75 mm
Min. bore diameter	5 mm
Machining direction	Left
Carbide type	HW56 15
Material to be processed	Stainless steel, Non-ferrous metal

EAN-Code

4050293379440