

3-jaw tapered rod lathe chuck DURO-T

Hand chuck in acc. with DIN 6350-1



Application:

Optimised for turning applications, which require extremely high clamping forces, maximum concentricity and reliable continuous repeatability.

Execution:

- Grease nipples with very easy access are located at each jaw position.
- Fast and regular lubrication to ensure a long service life
- For cylindrical self-centring adapter DIN 6350-1
- Large through-bore
- Chuck body surface hardened

Advantage:

- No longer necessary to dismantle the chuck before lubricating the guides.
- With visual jaw locking and jaw quick-change system

Delivery:

1 spanner, 1 set of fastening screws (DIN 6350-1) no. 22427 041-061 with undivided stepped jaws and no. 22428 041-051 with plain jaws and reverse top jaws



Art. no.	22428 041
Brand	RÖHM
Manufacturer Part Number	437490
Outer diameter	160 mm
Number of jaws	3
DIN	6350-1
Min./max. external clamping width	5-161 mm
Min./max. internal clamping width	67-174 mm
Clearance hole	42 mm
Max. rotation speed	5400
Pitch circle diameter	125 mm
Centring diameter	145 mm
Tension force	73 kN
Max. torque	120 Nm
Gross Weight	9.000 kg
Product Group	202

EAN

4019208227771