

Measuring probes type FNF

For coating thickness gauges in the 456C model series with separate sensor

elcometer®

Application:

Bigfoot™ sensor for high measuring certainty, for use with coating thickness gauges in the 456C model series with sensor inputs



Execution:

- Separate Bigfoot™ combination sensor for devices with F/NF sensors

Art. no.	45800 665
Brand	ELCOMETER
Manufacturer Part Number	T456CFNF1R
Model	T456CFNF1R
Probe design	FNF
Accuracy (+/-)	2.5 µm
Min./max. accuracy (+/-) in %	1-3 %
Min./max. layer thickness of measuring range	0-1500 µm
Layer thickness resolution	< 100 µm: 0.1 µm, > 100 µm: 1 µm
Probe diameter	6 mm
Probe working height	38 mm
Cable output direction	Radial
Suitable for	Iron, Non-ferrous
Gross Weight	0.197 kg
Product Group	451