


Datasheet

Item no. 1586461

V1_0617_02_EN



Dimensions

Positions	A	B	C	E	F
25	53.04	47.04	38.96	33.24	41.10

Dimensions

Positions	A±0.15	B±0.10	D±0.13	E±0.08	F±0.10
25	53.05	47.04	38.40	33.24	41.10

NOTES:

MATERIAL

1. Insulator Material: Glass-filled thermoplastic PBT, UL94V-0
2. Contact Material: Brass or Phosphor Bronze
3. Shell : Steel, 100 μ" Tin Over 50μ" min Copper
4. Clinch Nut : Brass, Nickel Plated
5. Contact plating : Gold flash full gold & selective 15u"Au

ELECTRICAL

1. Current Rating : 3AMP
2. Voltage Rating : 250V AC/rms 60Hz
3. Contact Resistance: 20mΩ
4. Insulation Resistance: 1000MΩ min at 500 VDC
5. Withstand Voltage: 1000V AC/rms 60Hz for 1 minute

ENVIRONMENTAL

1. Temperature Range: -20°C~+105°C
- UL No. E198287

NOTES:

MATERIAL

1. Insulator Material: Glass-filled thermoplastic PBT, UL94V-0, Gray
2. Contact Material: Copper alloy
3. Shell : Steel, 100 μ" Tin Over 50μ" min Copper
- ④ 4. Clinch Nut : Brass, Nickel Plated
5. Contact plating : Gold flash full gold

ELECTRICAL

1. Current Rating : 3AMP
 2. Voltage Rating : 250V AC/rms 60Hz
 3. Contact Resistance: 20mΩ Max at 1 AMP DC
 4. Insulation Resistance: 1000MΩ at 500 VDC
 - ② 5. Withstand Voltage: 1000V AC/rms 60Hz for 1 minute
 - ② 6. OPERATING TEMPERATURE: -20°C+105°C
- UL No. E198287

RoHS compliant
Unit:mm