DATA SHEET

THA01 PLUG MOUNTED MOVING AIR PROBE TYPE 'T'

PLUG MOUNTED MOVING AIR PROBE - Type 'T'

Description

Air probe plug mounted using a moulded connector.

Construction

Air probe with exposed thermocouple sensor protected by a funnelled stainless steel sheath. Insulated in ceramic sheaths.

Sensor stem is 4mm diameter and 100mm long, the sensor is approx 15mm from the stem end. Funnel measures $30mm \times 13mm$ diameter

Sensor Features

> TOTAL ENCAPSULATION TECHNIQUE FOR MAXIMUM STRENGTH AND DURABILITY.

This probe is manufactured using a two stage moulding technique. Firstly the probes are encased in tough nylon, then a thermoplastic over moulding is applied. This gives an extremely robust and durable construction with the added benefit that the assembly is waterproof.

> HIGH ACCURACY THERMOCOUPLE MATERIAL THROUGHOUT

Type 'T' Thermocouple : ½ Class I (±0.25°C ±0.15%)

WIDE AMBIENT TEMPERATURE SPECIFICATION : -50 TO 50 °C
TIME RESPONSE (96% of value in moving gas) : 0.1 Secs

➤ MEASUREMENT RANGE : -100 TO 400 °C

Cross-reference for compatible instruments

Suitable instruments for use with this probe

TME PART No	DESCRIPTION	APPLICATION
MM2000	SINGLE INPUT INSTRUMENT	HIGH ACCURACY TEMPERATURE MEASUREMENT
MM2010	MAX / MIN HOLD INSTRUMENT	HIGH ACCURACY INSTRUMENT WITH MAX, MIN AND HOLD FEATURES
MM2020	DIFFERENTIAL INSTRUMENT	DUAL INPUT INSTRUMENT FOR DIFFERENTIAL MEASUREMENTS
MM2030	THERMOCOUPLE SIMULATOR	HIGH ACCURACY SIMULATOR WITH MEASUREMENT FACILITY
MM7000-2D	BARCODE READING THERMOMETER	HIGH ACCURACY INSTRUMENT with BARCODE SCANNER & BLUETOOTH
SOLO-T	COMPACT SINGLE INPUT INSTRUMENT	HIGH ACCURACY TEMPERATURE MEASUREMENT