

W-Series
WPE 4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com


Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

| | |
|------------|---|
| Type | WPE 4 |
| Order No. | 1010100000 |
| Version | PE terminal, Screw connection, 4 mm ² , 480 A (4 mm ²), green / yellow |
| GTIN (EAN) | 4008190039820 |
| Qty. | 100 pc(s). |

W-Series
WPE 4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|--------------------------|---------|-----------------|------------|
| Width | 6.1 mm | Width (inches) | 0.24 inch |
| Height | 56 mm | Height (inches) | 2.205 inch |
| Depth | 46.5 mm | Depth (inches) | 1.831 inch |
| Depth including DIN rail | 47.5 mm | Net weight | 18.5 g |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|---------------------------|-------|--------|----------------|
| Material | Wemid | Colour | green / yellow |
| UL 94 flammability rating | V-0 | | |

Rating data IECEx/ATEX

| | | | |
|--------------------------------|---|---------------------------------|-------------------|
| Certificate No. (ATEX) | DEMKO14ATEX1338U | Certificate No. (IECEX) | IECEXULD14.0005U |
| Wire cross section max. (ATEX) | 4 mm ² | Wire cross section max. (IECEX) | 4 mm ² |
| Operating temperature range | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity | Marking EN 60079-7 | |
| Ex 2014/34/EU label | II 2 G D | | Ex e II |

System specifications

| | | | |
|--|--|------------------------------------|--------------|
| Version | Screw connection, With PE connection, closed | Tightening torque (mounting screw) | 0.4...0.8 Nm |
| Tightening torque (clamping screw for copper conductors) | 0.5...1 Nm | End cover plate required | No |
| Number of potentials | 1 | Number of levels | 1 |
| No. of clamping points per level | 2 | Number of potentials per tier | 1 |
| Levels cross-connected internally | No | PE connection | Yes |
| Mounting rail | TS 35 | N-function | No |
| PE function | Yes | PEN function | No |

Additional technical data

| | | | |
|--------------------------|------------------|-----------------------------|---------|
| Explosion-tested version | Yes | Installation advice | Screwed |
| Interlock | for screw fixing | Number of similar terminals | 1 |
| Open sides | closed | Type of mounting | Screwed |

CSA rating data

| | | | |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA) | 200039-1888378 | Wire cross section max. (CSA) | 10 AWG |
| Wire cross section min. (CSA) | 26 AWG | | |

W-Series
WPE 4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Conductors for clamping (rated connection)**

| | | | |
|---|----------------------|---|---------------------|
| Blade size | 0.6 x 3.5 mm | Clamping range, max. | 6 mm ² |
| Clamping range, min. | 0.13 mm ² | Clamping screw | M 3 |
| Connection cross-section, stranded, max. | 6 mm ² | Connection cross-section, stranded, min. | 0.5 mm ² |
| Connection direction | on side | Gauge to IEC 60947-1 | A4 |
| Number of connections | 2 | Stripping length | 10 mm |
| Tightening torque, max. | 1 Nm | Tightening torque, min. | 0.5 Nm |
| Torque level with DMS electric screwdriver | 2 | Type of connection | Screw connection |
| Wire connection cross section, finely stranded, max. | 6 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | Wire connection cross-section, finely stranded, min. | 0.5 mm ² |
| Wire connection cross-section, solid core, max. | 6 mm ² | Wire connection cross-section, solid core, min. | 0.5 mm ² |

Dimensions

| | |
|--------------|-------|
| TS 35 offset | 28 mm |
|--------------|-------|

PE rating data

| | | | |
|--|----------------------------|------------------------------|-------|
| Rated short-time current | 480 A (4 mm ²) | Centre screw on PE terminals | M 2.5 |
| Tightening torque range for fixing screw | 0.4...0.8 Nm | PEN function | No |

Rating data

| | | | |
|--|-------------------|--|-------|
| Rated cross-section | 4 mm ² | Rated voltage to adjoining terminal | 800 V |
| Standards | IEC 60947-7-2 | Volume resistance according to IEC 60947-7-x | 1 mΩ |
| Rated impulse withstand voltage to adjacent terminal | 8 kV | Pollution severity | 3 |

UL rating data

| | | | |
|---|--------|---|--------|
| Certificate No. (UR) | E60693 | Conductor size Factory wiring max. (UR) | 10 AWG |
| Conductor size Factory wiring min. (UR) | 26 AWG | Conductor size Field wiring max. (UR) | 10 AWG |
| Conductor size Field wiring min. (UR) | 22 AWG | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000901 | ETIM 4.0 | EC000491 |
| ETIM 5.0 | EC000491 | ETIM 6.0 | EC000901 |
| UNSPSC | 30-21-18-11 | eClass 5.1 | 27-14-03-05 |
| eClass 6.2 | 27-14-03-05 | eClass 7.1 | 27-14-03-05 |
| eClass 8.1 | 27-14-11-41 | eClass 9.0 | 27-14-11-41 |
| eClass 9.1 | 27-14-11-41 | | |

Product information

| | |
|------------------------------|--|
| Descriptive text accessories | Rail support protective insulation for installation of mounting rail "SH 2" order No. 0494920000 (QTY 10). |
|------------------------------|--|

Creation date July 2, 2018 10:59:54 AM CEST

Catalogue status 29.06.2018 / We reserve the right to make technical changes.

3

Data sheet

**W-Series
WPE 4**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | CFAT_WPE 4.pdf IECEXULD14.0005U_e.pdf DE_PT1002_20160418_936_ISSUE01.pdf ACF-ATEX_4786180920 |
| Brochure/Catalogue | CAT 5 ENCL 17/18 EN CAT 1 TERM 16/17 EN |
| Engineering Data | EPLAN_WSCAD_Zuken E3.S |
| User Documentation | NTI_IECEX_WDU-WPE 4.pdf |

Safety note

Safety notice [Safety Information](#)

Data sheet

W-Series
WPE 4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

