




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: .51 – 1.65 mm²

Mating Tab Width: 6.35 mm [.25 in]

Mating Tab Thickness: .81 mm [.032 in]

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Plating Material	Unplated

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle
Terminal Orientation	Straight
Contact Base Material	Brass



Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.31 – 3.3 mm [.091 – .13 in]
Overall Length	20.2 mm [.795 in]
Wire Size	.51 – 1.65 mm ²
Mating Tab Width	6.35 mm [.25 in]
Mating Tab Thickness	.81 mm [.032 in]

Usage Conditions

Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]
-----------------------------	-----------------------------

Industry Standards

UL Rating	Listed
CSA Certified	Yes

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece/Carton

Other

Line	Premier
------	---------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201)

	Candidate List Declared Against: JUL 2019 (201)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Model / Part # 9-1579022-1
CERTILOK DIE FASTON
6.3



TE Model / Part # 539740-2
DIE F6. 3FF REC.

Also in the Series | FASTON 250



Compression Connectors
(4)



Crimp Terminal Housings
(133)



Magnet Wire Terminals(1)



PCB Terminals(140)





Quick Disconnects(463)



Splices(4)

Customers Also Bought

TE Model / Part #726344-1
SO-RINGZUNGE D46234TE Model / Part #
5677622002
RNF-3000-1.5/0.5-2-STKTE Model / Part #1-160304-
0
FASTON 250 REC 1.0-2.5
MM2 BRTE Model / Part #5-160506-
2
FASTON 250 REC 0.5-1.5
MM2 TPBRTE Model / Part #1-925369-
4
MOD.IV.FEMHSG WITHTE Model / Part #2-
1437020-1
609-0631=FSKT IDC S 06
SRTE Model / Part #5-160491-
1
FASTON 187 REC 1.0-2.5
MM2 PLAIN BRTE Model / Part #
5677762002
RNF-3000-1.5/0.5-6-STK

Documents

Product Drawings

FASTON 250 RECEPTACLE 0.5-1.5 MM2 BR

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5-160506-1_A_c-5-160506-1-a.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-160506-1_A_c-5-160506-1-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-160506-1_A_c-5-160506-1-a.3d_stp.zip](#)

English



[Agency Approvals](#)

[UL Report](#)

English