

SVXC clamp holder, positive

for copy, longitudinal face lathing with VC indexable insert

ATORN[®]

Application


for copy, longitudinal and face turning with VC indexable insert, 35°

Version

- precision-manufactured steel support, bronzed, hardened, type V, working angle 113°, tip angle 35°, clearance angle 7°

Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces
- excellent surface quality for medium infeed and finishing
- Very good surface quality for medium infeed and finishing



Art. no.	17836 290
ISO name	SVXC R/L 12 12 F07
Shaft height	12 mm
Shank width	12 mm
Length	80 mm
Length of head	18 mm
Programming size	16 mm
Suitable for indexable inserts	VC.. 0702..
Tool design	Left

EAN-Code

4050293544077