

Belt sanding machine Panther



Application:

The belt sanding machines are suitable for the toughest applications in trade and industry. Equipped with S1 motors for 100% switch-on time. The capacity of S1 motors is 40% higher compared to S6 motors.

Version:

- adjustable working height
- S1 three-phase motor 400 V, 50 Hz
- for surface and contact grinding
- low-vibration
- removable protective cover for surface grinding
- connection for double suction system
- with emergency stop switch

Delivery:

with underframe, sanding belt, spark protection and connection cable for optional fixed connection or CEE plug.



Art. no.	78236 010
Model	75/1/3
Max. sanding belt width	75 mm
Grinding belt length	2000 mm
Max. belt speed	33 m/s
Motor speed	2800 rpm
Motor output	3 kW
Weight	90 kg

EAN-Code

4251770600150