


1

Resistor - Weerstand - Résistance - Widerstand - Resistencia - Motstand - Vastus - Resistenze




R1, R2, R3, R4: 2K2 | (Red, Red, Red) -(Rood, Rood, Rood) -(Rouge, Rouge, Rouge) -(Rot, Rot, Rot) (Röd, Röd, Röd) -(Punainen, Punainen, Punainen) -(Rojo, Rojo, Rojo) -(Encarnado, Encarnado, Encarnado) -(Rosso, Rosso, Rosso)

R5: 0 | (Black) -(zwart) -(noir) -(Schwarz) -(Svart) -(Musta) -(Negro) -(Preto) -(Nero)

R6, R7, R8, R9, R10, R11: 100 | (Brown, Black, Brown) -(Bruin, zwart, Brown) -(Brun, noir, Brun) -(Braun, Schwarz, Braun) -(Brun, Svart, Brun) -(Ruskea, Musta, Ruskea) -(Marrón, Negro, Marrón) -(Castanho, Preto, Castanho) -(Marrone, Nero, Marrone)


R12, R13, R14: 10K | (Brown, Black, Orange) -(Bruin, zwart, Oranje) -(Brun, noir, Orange) -(Braun, Schwarz, Orange) -(Brun, Svart, Orange) -(Ruskea, Musta, Oranssi) -(Marrón, Negro, Naranja) -(Castanho, Preto, Laranja) -(Marrone, Nero, Aranciato)

2 DIODE




◇ D1...D21: 1N4148
Watch the polarity!
Att. la polarité!

3 CAPACITORS




◇ C1, C2: 100n (104, µ1)

4 SWITCH




◇ SW1

5 TRIMMER



◇ RV1: 220K (250K)

6 IC SOCKET




◇ IC1

WATCH THE POSITION OF THE NOTCH!


ATTENTION A LA POSITION DE L'ENCOCHE!

7 TRANSISTORS



◇ T1: BC547
◇ T2: BC547
◇ T3: BC557

8 ELECTROLYTIC CAPACITORS




◇ C3, C4: 47µF
◇ C5: 100µF

Watch the polarity!

Attention à la polarité!


9 IC SOCKET AND IC




◇ IC1: 4017

WATCH THE POSITION OF THE NOTCH!


ATTENTION A LA POSITION DE L'ENCOCHE!



11 LEDS



10 BATTERY HOLDER



9V Battery

