SIEMENS

Data sheet 6GT2398-1DA00

product type designation



ANT 18 antenna stainless steel, without cable

SIMATIC RF300/RF200 antenna ANT 18 stainless steel, -25...+70 $^{\circ}$ C, IP65, thread M18x1, length 40 mm; without connection cable.

suitability for operation	RF250R / RF350R / RF350M
radio frequencies	
transmission frequency / rated value	13.56 MHz
electrical data	
type of electrical connection / of the antenna	M8, 4-pin
design of plug-in connection	female
mechanical data	
material	Stainless steel V2A
color	Silver
tightening torque / of the screw for securing the equipment / maximum	3 N·m
mounting distance	
 relating to metal surfaces / recommended / minimum 	0 m
ambient conditions	
ambient temperature	
 during operation 	-25 +70 °C
 during storage 	-40 +85 °C
 during transport 	-40 +85 °C
protection class IP	IP67
shock acceleration	500 m/s²
vibrational acceleration	200 m/s ²
design, dimensions and weights	
depth	40 mm
diameter	18 mm
net weight	40 g
fastening method	2 x stainless steel nuts M18 x 1
standards, specifications, approvals	
certificate of suitability	CE, cULus
certificate of suitability	
• IECEx	Yes
• for IECEx / as marking	the ATEX approval of the connected reader applies
reference code	
according to IEC 81346-2	TF
• according to IEC 81346-2:2019	TFB
accessories	
accessories	Antenna cable
further information / internet-Links	

Internet-Link

• to web page: selection aid TIA Selection Tool

• to website: Industrial communication

• to website: Industry Mall

• to website: Information and Download Center

• to website: Image database

to website: CAx-Download-Managerto website: Industry Online Support

last modified:

https://support.industry.siemens.com/cs/ww/en/view/67384964

 $\underline{http://www.siemens.com/ident/rfid}$

https://mall.industry.siemens.com

http://www.siemens.com/industry/infocenter

http://automation.siemens.com/bilddb

http://www.siemens.com/cax

https://support.industry.siemens.com

11/3/2021