

















## Heatsinks for transistors in plastic case

<b>art. no.</b>   <b>FK 227 SA L 1</b>		 <p>22 K/W   TO 220</p>	
<b>art. no.</b>   <b>FK 238 SA L 1</b>		 <p>12 K/W   TO 220</p>	
<b>material:</b> <b>surface:</b>		aluminium black anodised	
<b>art. no.</b>   <b>FK 218 32 ...</b>		 <p>21 K/W   SOT 32   TO 220</p>	
<b>art. no.</b>   <b>FK 232 220 ...</b>		 <p>21 K/W   TO 220</p>	
<b>art. no.</b>   <b>FK 233 220 ...</b>		 <p>20,2 K/W   TO 220</p>	
<b>please indicate:</b> ... surface <b>SA</b> = black anodised <b>MI</b> = solderable surface			
<b>material:</b>		aluminium	