

General Information

Extended Product Type:	AF80-30-00-14
Product ID:	1SBL397001R1400
EAN:	3471523132948
Catalog Description:	AF80-30-00-14 250-500V50/60HZ-DC Contactor
Long Description:	AF80 contactors are used for controlling power circuits up to 690 V AC and 220 V DC. They are mainly used for controlling 3-phase motors, non-inductive or slightly inductive loads. AF... contactors include an electronic coil interface accepting a wide control voltage U_c min. ... U_c max. Only four coils cover control voltages between 24...500 V 50/60 Hz or 20...500 V DC. AF contactors can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. AF contactors have built-in surge protection and do not require additional surge suppressors. The AF... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles, front and side-mounted add-on auxiliary contact blocks (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1. N.C. mirror contacts compliant with Annex F of IEC 60947-4-1) - Control circuit: AC or DC operated - Accessories: a wide range of accessories is available.

Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Block Contactors

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369085
EAN:	3471523132948

Dimensions

Product Net Depth:	116 mm
Product Net Height:	125.5 mm
Product Net Weight:	1.170 kg
Product Net Width:	70 mm

Container Information

Package Level 1 Width:	150 mm
Package Level 1 Length:	150 mm
Package Level 1 Height:	103 mm
Package Level 1 Gross Weight:	1.29 kg
Package Level 1 EAN:	3471523132948
Package Level 2 Units:	8 piece
Package Level 2 Width:	250 mm
Package Level 2 Length:	300 mm
Package Level 2 Height:	300 mm
Package Level 3 Units:	192 piece
Package Level 1 Units:	1 piece

Technical

Number of Main Contacts NC:	0
Number of Auxiliary Contacts NO:	0
Number of Auxiliary Contacts NC:	0
Rated Operational Voltage:	Main Circuit 690 V
Rated Frequency (f):	Main Circuit 50 / 60 Hz
Conventional Free-air Thermal Current (I_{th}):	acc. to IEC 60947-4-1, Open Contactors $q = 40$ °C 130 A
Rated Operational Current AC-1 (I_e):	(690 V) 40 °C 125 A (690 V) 60 °C 100 A (690 V) 70 °C 85 A
Rated Operational Current AC-3 (I_e):	(220 / 230 / 240 V) 60 °C 80 A (380 / 400 V) 60 °C 80 A (415 V) 60 °C 80 A (440 V) 60 °C 80 A (500 V) 60 °C 65 A (690 V) 60 °C 49 A (1000 V) 60 °C 25 A
Rated Operational Power AC-3 (P_e):	(220 / 230 / 240 V) 22 kW (380 / 400 V) 37 kW (400 V) 37 kW

(415 V) 45 kW
(440 V) 45 kW
(500 V) 45 kW
(690 V) 45 kW

Rated Short-time Withstand Current (I_{cw}):	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 780 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 140 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 300 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 1200 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 450 A
Maximum Breaking Capacity:	cos phi=0.45 (cos phi=0.35 for $I_e > 100$ A) at 440 V 1150 A cos phi=0.45 (cos phi=0.35 for $I_e > 100$ A) at 690 V 750 A
Maximum Electrical Switching Frequency:	AC-1 600 cycles per hour AC-2 / AC-4 150 cycles per hour AC-3 1200 cycles per hour
Rated Insulation Voltage (U_i):	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8 kV
Maximum Mechanical Switching Frequency:	3600 cycles per hour
Rated Control Circuit Voltage (U_c):	50 Hz 250 ... 500 V 60 Hz 250 ... 500 V DC Operation 250 ... 500 V
Operate Time:	Between Coil De-energization and NC Contact Closing 19 ... 105 ms Between Coil De-energization and NO Contact Opening 17 ... 100 ms Between Coil Energization and NC Contact Opening 38 ... 95 ms Between Coil Energization and NO Contact Closing 42 ... 100 ms
Connecting Capacity Main Circuit:	Flexible with Insulated Ferrule 1/2x 6...50 mm ² Flexible with Ferrule 1/2x 6...50 mm ² Rigid 1x 6...70 mm ² Rigid 2x 6...50 mm ²
Connecting Capacity Control Circuit:	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm ² Rigid 1/2x 1 ... 2.5 mm ²
Wire Stripping Length:	Main Circuit 17 mm
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
Terminal Type:	Screw Terminals
Number of Main Contacts NO:	3

Environmental

Climatic Withstand:	Category B according to IEC 60947-1 Annex Q
Maximum Operating Altitude Permissible:	3000 m
Resistance to Vibrations acc. to IEC 60068-2-6:	5 ... 300 Hz 3 g closed position / 3 g open position
Resistance to Shock acc. to IEC 60068-2-27:	Closed, Shock Direction: A 25 g Closed, Shock Direction: B1 25 g Closed, Shock Direction: B2 15 g Closed, Shock Direction: C1 25 g Closed, Shock Direction: C2 25 g Open, Shock Direction: B1 5 g
Ambient Air Temperature:	Close to Contactor for Storage -60...+80 °C Close to Contactor Fitted with Thermal O/L Relay -25 ... +60 °C Close to Contactor without Thermal O/L Relay -40 ... +70 °C

Technical UL/CSA

General Use Rating UL/CSA:	(600 V AC) 105 A
Horsepower Rating UL/CSA:	(120 V AC) Single Phase 7-1/2 Hp (240 V AC) Single Phase 15 Hp (200 ... 208 V AC) Three Phase 25 Hp (220 ... 240 V AC) Three Phase 30 Hp (440 ... 480 V AC) Three Phase 60 Hp (550 ... 600 V AC) Three Phase 75 Hp
Tightening Torque UL/CSA:	Control Circuit 11 in·lb Main Circuit 53 in·lb

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SBC101036M6801
ABS Certificate:	ABS_15-GE1349500-PDA_90682247
BV Certificate:	BV_2634H36994A
CB Certificate:	CB_SE-77417M1
CCC Certificate:	CCC_2013010304646569

Data Sheet, Technical Information:	1SBC100173C0201
Declaration of Conformity - CE:	1SBD250000U1000
DNV Certificate:	DNV-GL_E13871
EAC Certificate:	EAC_RU C-FR ME77 B01010
GL Certificate:	DNV-GL_E13871
LR Certificate:	LRS_1300087E1
RINA Certificate:	RINA_ELE084013XG
RMRS Certificate:	RMRS_1400682124
RoHS Information:	1SBD251021E1000
UL Certificate:	UL_20130926-E312527_14_1
UL Listing Card:	UL_E312527

Classifications

E-nummer:	3210054
ETIM 4:	EC000066 - Magnet contactor, AC-switching
ETIM 5:	EC000066 - Magnet contactor, AC-switching
ETIM 6:	EC000066 - Power contactor, AC switching
UNSPSC:	39121529
Object Classification Code:	Q

