



SINAUT ST7, TIM 3V-IE COMMUNICATION MODULE FOR SIMATIC S7-300 WITH A RS232-INTERFACE FOR SINAUT COMMUNICATION VIA A CLASSIC WAN AND A RJ45 INTERFACE FOR SINAUT COMMUNICATION VIA AN IP-BASED NETWORK (WAN OR LAN)

### Transmission rate

#### Transfer rate

- |   |                    |
|---|--------------------|
| <ul style="list-style-type: none"> <li>for Industrial Ethernet</li> </ul> | 10 ... 100 Mbit/s  |
| <ul style="list-style-type: none"> <li>acc. to RS 232</li> </ul>          | 50 ... 38400 bit/s |

### Interfaces

|   |                                |
|---|--------------------------------|
| Number of interfaces / acc. to Industrial Ethernet  | 1                              |
| Number of electrical connections  |                                |
| <ul style="list-style-type: none"> <li>for external data transmission / acc. to RS 232</li> </ul> | 1                              |
| <ul style="list-style-type: none"> <li>for power supply</li> </ul>                                | 1                              |
| Type of electrical connection   |                                |
| <ul style="list-style-type: none"> <li>of Industrial Ethernet interface</li> </ul>                | RJ45 port                      |
| <ul style="list-style-type: none"> <li>at interface 1 / for external data transmission</li> </ul> | 9 pin Sub-D-connector (RS232)  |
| <ul style="list-style-type: none"> <li>for power supply</li> </ul>                                | 2-pole plugable terminal block |
| design of the removable storage / C-PLUG  | No                             |

### Supply voltage, current consumption, power loss

|  |                 |
|--|-----------------|
| Type of voltage / of the supply voltage                  | DC              |
| Supply voltage   | 24 V            |
| Supply voltage   | 20.4 ... 28.8 V |
| Relative symmetrical tolerance / for DC                  |                 |
| <ul style="list-style-type: none"> <li>at 5 V</li> </ul> | 5 %             |
| Relative positive tolerance / for DC / at 24 V           | 5 %             |
| Relative negative tolerance / for DC / at 24 V           | 5 %             |
| Consumed current   |                 |

|   |       |
|---|-------|
| <ul style="list-style-type: none"> <li>• from backplane bus / for DC / at 24 V / maximum</li> </ul>           | 0.2 A |
| <ul style="list-style-type: none"> <li>• from external supply voltage / for DC / at 24 V / maximum</li> </ul> | 0.2 A |
| Active power loss   | 5.8 W |
| Product expansion / optional / Backup battery   | No    |

#### Permitted ambient conditions

|  |                |
|--|----------------|
| Ambient temperature  |                |
| <ul style="list-style-type: none"> <li>• during operation</li> </ul>             | 0 ... 60 °C    |
| <ul style="list-style-type: none"> <li>• during storage</li> </ul>               | -40 ... +70 °C |
| <ul style="list-style-type: none"> <li>• during transport</li> </ul>             | -40 ... +70 °C |
| Relative humidity / at 25 °C / without condensation / during operation / maximum | 95 %           |
| Protection class IP  | IP20           |

#### Design, dimensions and weight

|               |                                    |
|---------------|------------------------------------|
| Module format | Compact module S7-300 single width |
| Width         | 40 mm                              |
| Height        | 125 mm                             |
| Depth         | 120 mm                             |
| Net weight    | 0.25 kg                            |

#### Product properties, functions, components / general

|   |                              |
|---|------------------------------|
| Number of units   |                              |
| <ul style="list-style-type: none"> <li>• per CPU / maximum</li> </ul>               | 1                            |
| <ul style="list-style-type: none"> <li>• Note</li> </ul>                            | Number of TIMs per S7-300: 1 |
| Cable length  |                              |
| <ul style="list-style-type: none"> <li>• with RS 232 interface / maximum</li> </ul> | 6 m                          |

#### Performance data / S7 communication

|   |     |
|---|-----|
| Number of possible connections / for S7 communication                               |     |
| <ul style="list-style-type: none"> <li>• maximum</li> </ul>                         | 8   |
| <ul style="list-style-type: none"> <li>• with PG connections / maximum</li> </ul>   | 2   |
| <ul style="list-style-type: none"> <li>• with OP connections / maximum</li> </ul>   | 8   |
| Service   |     |
| <ul style="list-style-type: none"> <li>• SINAUT ST7 via S7 communication</li> </ul> | Yes |
| <ul style="list-style-type: none"> <li>• PG/OP communication</li> </ul>             | Yes |

#### Performance data / multi-protocol mode

|   |    |
|---|----|
| Number of active connections / with multi-protocol mode | 12 |
|---|----|

#### Performance data / telecontrol

|  |    |
|--|----|
| Suitability for use  |    |
| <ul style="list-style-type: none"> <li>• Node station</li> </ul> | No |

|  |  |
|--|--|
| <ul style="list-style-type: none"> <li>• substation</li> <li>• TIM control center</li> <li>• Note</li> </ul>   | <p>Yes</p> <p>No</p> <p>RS232 and Industrial Ethernet can not be operated in parallel</p>  |
| <p>Protocol / is supported</p> <ul style="list-style-type: none"> <li>• TCP/IP</li> <li>• DNP3</li> <li>• SINAUT ST1 protocol</li> <li>• SINAUT ST7 protocol</li> </ul>  | <p>Yes</p> <p>No</p> <p>Yes</p> <p>Yes</p>   |
| <p>Product function / data buffering if connection is aborted</p> <ul style="list-style-type: none"> <li>• Note</li> </ul>   | <p>Yes</p> <p>16,000 data messages</p>   |
| <p>Storage capacity</p> <ul style="list-style-type: none"> <li>• of S7 CPU RAM / for TD7onCPU mode data blocks on CPU / required</li> <li>• of S7 CPU RAM / for TD7onTIM mode data blocks on TIM / required</li> <li>• Note</li> </ul>   | <p>20 Kibyte</p> <p>0 Kibyte</p> <p>TD7onCPU: at least 20 KB, actual requirement determined by data volume and functional scope TD7onTIM: 0 bytes in most favorable case</p>           |
| <p>Product property / Buffered message frame memory</p>  | <p>No</p>  |
| <p>Transmission format</p> <ul style="list-style-type: none"> <li>• for SINAUT ST1 protocol with polling / 11 bit</li> <li>• for SINAUT ST1 protocol with spontaneous / 10-bit or 11-bit</li> <li>• for SINAUT ST7 protocol with multi-master polling / 10-bit</li> <li>• for SINAUT ST7 protocol with polling or spontaneous / 10-bit or 11-bit</li> </ul>      | <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>  |
| <p>Operating mode for scanning of data transmission</p> <ul style="list-style-type: none"> <li>• with dedicated line/radio link / with SINAUT ST1 protocol</li> <li>• with dedicated line/radio link / with SINAUT ST7 protocol</li> <li>• with dial-up network / with SINAUT ST1 protocol</li> <li>• with dial-up network / with SINAUT ST7 protocol</li> </ul> | <p>Polling, polling with time slot procedure</p> <p>Polling, polling with time slot procedure, multi-master polling with time slot procedure</p> <p>spontaneous</p> <p>spontaneous</p> |
| <p>Hamming distance</p> <ul style="list-style-type: none"> <li>• for SINAUT ST1 protocol</li> <li>• for SINAUT ST7 protocol</li> </ul>   | <p>4</p> <p>4</p>  |
| <p><b>Product functions / management, configuration</b></p>  |  |
| <p>Configuration software</p> <ul style="list-style-type: none"> <li>• required</li> </ul>   | <p>SINAUT ST7 ES</p>   |

|  |            |
|--|------------|
| <ul style="list-style-type: none"> <li>• for CPU configuring / required / SINAUT TD7 block library for CPU</li> </ul>        | Yes        |
| <ul style="list-style-type: none"> <li>• for PG configuring / required / SINAUT ST7 configuration software for PG</li> </ul> | Yes        |
| Storage location / of TIM configuration data   | On the TIM |

### Product functions / Security

|   |  |
|---|--|
| Suitability for operation / Virtual Private Network   | Yes  |
| Operating mode Virtual Private Network / note   | VPN operation as MSC client with MSC protocol and password protection only possible in conjunction with GPRS modem with MSC capability |
| Type of authentication / with Virtual Private Network / PSK                                       | Yes  |
| Product function  |  |
| <ul style="list-style-type: none"> <li>• password protection for VPN</li> </ul>                   | Yes  |
| <ul style="list-style-type: none"> <li>• MSC client via GPRS modem with MSC capability</li> </ul> | Yes  |
| Protocol  |  |
| <ul style="list-style-type: none"> <li>• is supported / MSC protocol</li> </ul>                   | No   |
| Key length / for MSC / with Virtual Private Network   | 128 bit  |
| Number of possible connections  |  |
| <ul style="list-style-type: none"> <li>• as MSC client / with VPN connection</li> </ul>           | 1  |
| <ul style="list-style-type: none"> <li>• as MSC server / with VPN connection</li> </ul>           | 0  |

### Further Information / Internet Links

|   |   |
|---|---|
| Internet-Link   |   |
| <ul style="list-style-type: none"> <li>• to website: Selector SIMATIC NET SELECTION TOOL</li> </ul> | <a href="http://www.siemens.com/snst">http://www.siemens.com/snst</a>                                     |
| <ul style="list-style-type: none"> <li>• to website: Industrial communication</li> </ul>            | <a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>                       |
| <ul style="list-style-type: none"> <li>• to website: Industry Mall</li> </ul>                       | <a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>                         |
| <ul style="list-style-type: none"> <li>• to website: Information and Download Center</li> </ul>     | <a href="http://www.siemens.com/automation/net/catalog">http://www.siemens.com/automation/net/catalog</a> |
| <ul style="list-style-type: none"> <li>• to website: Image database</li> </ul>                      | <a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>                   |
| <ul style="list-style-type: none"> <li>• to website: CAx Download Manager</li> </ul>                | <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>                                       |
| <ul style="list-style-type: none"> <li>• to website: Industry Online Support</li> </ul>             | <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>                   |

### Security information

---

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

**last modified:**

12.03.2015