



Finish : Reflector

1	0833	2	0833	3	0000	4		5		6		7		8
SUPERSEDES 9238 527 44500 0833/000 p.190-1 Of 18/10/2010		HALOGEN LAMP INFRARED INDUSTRIAL REFLECTOR 13169Z/98 500W 235V REFL				9238 527 44500 0833/000			22/03/2012					
REF. : PDM IRK 2012-022		DOCUMENTATION		UNIT mm	PROJ. EUROP 	2 SH	SH 190-2	10	1:1	A4				
NAME : J.P. CHARLIER		VALIDATION : A. PICHARD			DR. FISCHER Europe									
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.														

PRODUCT REQUIREMENT SHEET

See LV 75-032

MEASURING VOLTAGE	235V (stabilisation 3 min.)
MEASURING POSITION	Horizontal
LIFE TEST POSITION	Horizontal
BURNING POSITION	P15
SWITCHING CYCLE	Continuous
AGEING	1h at rated voltage

	VALUE UNIT	TOLERANCE
WATTAGE	500W	± 6 %
LIFE	5000 h	average
COLOR TEMPERATURE	Clear lamp Lamp with reflector	2400 K 2300 K ± 100 K Indicative value
FLUX (HeLeN lamp)	Clear lamp Reduction	NA NA
WEIGHT	36 g	

1	0833	2	0833	3	0000	4		5		6		7		8		
SUPERSEDES :		HALOGEN LAMP						9238 527 44500		22/03/2012						
9238 527 44500		INFRARED INDUSTRIAL REFLECTOR						0833/000								
0833/000 p. 190-2		13169Z/98 500W 235V														
Of 18/10/2010		REF. : PDM IRK 2012-022		DOCUMENTATION		UNIT	mm	PROJ	EUROP	2	SH	SH	190-2	10	A4	
NOM : J.P. CHARLIER		VALIDATION : A. PICHARD						DR. FISCHER Europe								
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.																