



**Phase busbar, 4-phases, 16qmm, pin, 1m**

**Part no. Z-SV-16/3P+3N-3TE**  
**Article no. 264915**

## Technical data ETIM 6.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Phase busbar (ecl@ss8.1-27-37-13-06 [ACN992008])			
Number of phases			3
Number of poles			3
Suitable for number of devices			0
Pitch dimensions		mm	17.95
Cross section		mm <sup>2</sup>	16
Length		mm	1000
Number of modular spacings			3
Rated permanent current I <sub>u</sub>		A	63
Type of electric connection			Pin
Insulated			Yes
Rated surge voltage		kV	4
Conditioned rated short-circuit current I <sub>q</sub>		kA	0
Max. rated operation voltage U <sub>e</sub>		V	415
Rated short-time withstand current I <sub>cw</sub>		kA	0
Suitable for devices with N-busbar			No
Suitable for devices with auxiliary switch			No