

Boring bar holder, shape E2

For turning tools with cylindrical shanks

ORION[®]

Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm²
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground
- Internal and external coolant supply



| | |
|---------------------------------|------------------|
| Art. no. | 22778 109 |
| Brand | ORION |
| Manufacturer Part Number | 22778109 |
| VDI mount diameter | 30 mm |
| Clamping diameter | 12 mm |
| Length | 22 mm |
| Outer diameter | 55 mm |
| Projecting length | 60 mm |
| Gross Weight | 1.495 kg |
| Product Group | 2AC |

EAN

4053625465071