

Collet type ER



Application:

For drilling and centring tools.

Execution:

- For NC lathes
- Burnished
- For suitable collets, see no. 23320
- No. 23308 008-020 ring profile key for tightening and loosening.

| | |
|---------------------------------|------------------|
| Art. no. | 22782 030 |
| Brand | EWS |
| Manufacturer Part Number | 135938 |
| VDI mount diameter | 30 mm |
| Collet type | ER 25 |
| Min./max. clamping range | 1-16 mm |
| Projecting length | 57 mm |
| Outer diameter | 68 mm |
| Gross Weight | 0.899 kg |
| Product Group | 215 |

