



MASTER - LED HID SON-T - Ultra Efficient

MAS LED SON-T UE M 6Klm 28.5W 740 E27

Philips MASTER - LED HID SON-T Ultra Efficient lamps are an easy LED solution with the highest efficiency to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. MASTER – LED HID SON-T UE solutions bring the energy efficiency and long lifetime benefits of LED to HID replacement, providing instant savings for low energy costs. With the right lamp size and light distribution, you can easily use MASTER – LED HID SON-T UE lamps into existing SON and SON-T systems, enhancing the lighting quality with LED by removing the luminaire's ballast for direct Mains working, gaining additional savings.

Warnings and Safety

- Installation should always be performed by a qualified electrician or installer. Use the installation guide for instructions.

Product data

General Information		Light Technical	
Cap-Base	E27	Color Code	740 [CCT of 4000K]
Nominal lifetime	50,000 hour(s)	Beam Angle (Nom)	300 degree(s)
Switching Cycle	50,000	Luminous Flux	6,000 lm
Lighting Technology	LED	Color Designation	Cool White (CW)
Flux measurement reference	Sphere	Correlated Color Temperature (Nom)	4000 K
Value ladder	Performance	Luminous Efficacy (rated) (Nom)	210 lm/W
CE mark	Yes	Color Consistency	<6
EU RoHS compliant	Yes	Color rendering index (CRI)	70
		LLMF At End Of Nominal Lifetime (Nom)	70 %

MASTER - LED HID SON-T - Ultra Efficient

Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	2
Photobiological safety according to EN 62471	RG1


Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	28.5 W
Lamp Current (Nom)	125 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Voltage (Nom)	220 V
Inrush current at mains	29.7
Max. lamp no. on MCB B type 10A - Mains	7
Max. lamp no. on MCB B type 10A - EM ballast without Comp. Cap.	-
Max. lamp no. on MCB B type 10A - EM ballast with Comp. Cap.	-
Max. lamp no. on MCB B type 16A - Mains	12
Max. lamp no. on MCB B type 16A - EM ballast without Comp. Cap.	-
Max. lamp no. on MCB B type 16A - EM ballast with Comp. Cap.	-
Ballast Compatibility	Mains

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Dimensional drawing



T-Case Maximum (Nom)	41.51 °C
----------------------	----------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T46

Approval and Application

Energy Efficiency Class	A
Energy Consumption kWh/1000 h	29 kWh
EPREL Registration Number	1552688



Product Data

Order product name	MAS LED SON-T UE M 6Klm 28.5W 740 E27
Full product name	MAS LED SON-T UE M 6Klm 28.5W 740 E27
Full product code	872016924035300
Order code	929003677402
Material Nr. (12NC)	929003677402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169240353
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169240360

Product	D	C
MAS LED SON-T UE M 6Klm 28.5W 740 E27	47 mm	237 mm


MASTER - LED HID SON-T - Ultra Efficient

Photometric data




Light Distribution Diagram - MAS LED SON-T UE M 6Klm 28.5W 740 E27

General uniform lighting - MAS LED SON-T UE M 6Klm 28.5W 740 E27




Spectral Power Distribution Colour - MAS LED SON-T UE M 6Klm 28.5W 740 E27

Lifetime



Life Expectancy Diagram - MAS LED SON-T UE M 6Klm 28.5W 740 E27



Lumen Maintenance Diagram - MAS LED SON-T UE M 6Klm 28.5W 740 E27

MASTER - LED HID SON-T - Ultra Efficient

