


COMPLIANT

Power MOSFET

PRODUCT SUMMARY				
V _{DS} (V)	60			
R _{DS(on)} (Ω)	V _{GS} = 10 V 0.028			
Q _g (Max.) (nC)	67			
Q _{gs} (nC)	18			
Q _{gd} (nC)	25			
Configuration	Single			



FEATURES

- Advanced Process Technology
- Ultra Low On-Resistance
- Dynamic dV/dt Rating
- 175 °C Operating Temperature
- Fast Switching
- Fully Avalanche Rated
- Drop in Replacement of the IRFZ44, SiHFZ44 for Linear/Audio Applications
- Compliant to RoHS Directive 2002/95/EC

DESCRIPTION

Advanced Power MOSFETs from Vishay utilize advanced processing techniques to achieve extremely low on-resistance per silicon area. This benefit, combined with the fast switching speed and ruggedized device design that Power MOSFETs are well known for, provides the designer with an extremely efficient and reliable device for use in a wide variety of applications.

The TO-220AB package is universally preferred for all commercial-industrial applications at power dissipation levels to approximately 50 W. The low thermal resistance and low package cost of the TO-220AB contribute to its wide acceptance throughout the industry.

ORDERING INFORMATION	
Package	TO-220AB
Lead (Pb)-free	IRFZ44RPbF
Leau (Fb)-nee	SiHFZ44R-E3
SnPb	IRFZ44R
SIFD	SiHFZ44R

PARAMETER			SYMBOL	LIMIT	UNIT	
Drain-Source Voltage			V_{DS}	60	V	
Gate-Source Voltage			V_{GS}	± 20	V	
Continuous Drain Currente	V _{GS} at 10 V	T _C = 25 °C T _C = 100 °C	,	50	А	
Continuous Drain Current	V _{GS} at 10 V	T _C = 100 °C	C ID	36		
Pulsed Drain Current ^a			I _{DM}	200		
Linear Derating Factor				1.0	W/°C	
Single Pulse Avalanche Energy ^b			E _{AS}	100	mJ	
Maximum Power Dissipation	pation T _C = 25 °C			150	W	
Peak Diode Recovery dV/dt ^c			dV/dt	4.5	V/ns	
Operating Junction and Storage Temperature Range			T _J , T _{stg}	- 55 to + 175	°C	
Soldering Recommendations (Peak Temperature) ^d	for 10 s			300	7	
Mounting Torque	6-32 or M3 screw			10	lbf ⋅ in	
Mounting Torque				1.1	N⋅m	

Notes

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).
- b. V_{DD} = 25 V, starting T_J = 25 °C, L = 44 μ H, R_g = 25 Ω , I_{AS} = 51 Å (see fig. 12).
- c. $I_{SD} \le 51 \text{ A}$, $dV/dt \le 250 \text{ A/}\mu\text{s}$, $V_{DD} \le V_{DS}$, $T_{J} \le 175 \text{ °C}$.
- d. 1.6 mm from case.
- e. Current limited by the package, (die current = 51 A).

^{*} Pb containing terminations are not RoHS compliant, exemptions may apply



THERMAL RESISTANCE RATINGS					
PARAMETER	SYMBOL	TYP.	MAX.	UNIT	
Maximum Junction-to-Ambient	R _{thJA}	-	62		
Case-to-Sink, Flat, Greased Surface	R _{thCS}	0.50	-	°C/W	
Maximum Junction-to-Case (Drain)	R _{thJC}	-	1.0		

PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT
Static						•	
Drain-Source Breakdown Voltage	V _{DS}	V _{GS} = 0	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		-	-	V
V _{DS} Temperature Coefficient	$\Delta V_{DS}/T_{J}$	Reference t	Reference to 25 °C, I _D = 1 mA		0.060	-	V/°C
Gate-Source Threshold Voltage	V _{GS(th)}	$V_{DS} = V_0$	_{GS} , I _D = 250 μA	2.0	-	4.0	V
Gate-Source Leakage	I _{GSS}	Vo	V _{GS} = ± 20		-	± 100	nA
Zaus Cata Valta as Dusin Courset		$V_{DS} = 60 \text{ V}, V_{GS} = 0 \text{ V}$		-	-	25	
Zero Gate Voltage Drain Current	I _{DSS}	$V_{DS} = 48 \text{ V}, V_{0}$	_{GS} = 0 V, T _J = 150 °C	-	-	250	μA
Drain-Source On-State Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 31 A ^b	-	-	0.028	Ω
Forward Transconductance	9 _{fs}	V _{DS} = 2	5 V, I _D = 31 A ^b	15	-	-	S
Dynamic							
Input Capacitance	C _{iss}	V	_{GS} = 0 V,	-	1900	-	pF
Output Capacitance	C _{oss}	V	os = 25 V,	-	920	-	
Reverse Transfer Capacitance	C _{rss}	f = 1.0 ľ	f = 1.0 MHz, see fig. 5		170	-	1
Total Gate Charge	Qg			-	-	67	
Gate-Source Charge	Q _{gs}	V _{GS} = 10 V	$V_{GS} = 10 \text{ V}$ $I_D = 51 \text{ A, } V_{DS} = 48 \text{ V,}$ see fig. 6 and 13 ^b		-	18	nC
Gate-Drain Charge	Q _{gd}				-	25	
Turn-On Delay Time	t _{d(on)}			-	14	-	
Rise Time	t _r	$V_{DD}=30~V,~I_D=51~A,$ $R_g=9.1~\Omega,~R_D=0.55~\Omega,~see~fig.~10^b$		-	110	-	ns
Turn-Off Delay Time	t _{d(off)}			-	45	-	
Fall Time	t _f			-	92	-	
Internal Drain Inductance	L _D	Between lead, 6 mm (0.25") from package and center of die contact		-	4.5	-	nH
Internal Source Inductance	L _S			-	7.5	-	11111
Drain-Source Body Diode Characteristic	s						
Continuous Source-Drain Diode Current	I _S	MOSFET symbol showing the integral reverse p - n junction diode		-	-	50°	^
Pulsed Diode Forward Current ^a	I _{SM}			-	-	200	A
Body Diode Voltage	V _{SD}	T _J = 25 °C, I _S	T _J = 25 °C, I _S = 51 A, V _{GS} = 0 V ^b		-	2.5	V
Body Diode Reverse Recovery Time	t _{rr}	- T _J = 25 °C, I _F = 51 A, dl/dt = 100 A/μs ^b		-	120	180	ns
Body Diode Reverse Recovery Charge	Q _{rr}			-	0.53	0.80	μC
Forward Turn-On Time	t _{on}	Intrinsic turn-	on is do	minated b	v Ls and	T D)	

Notes

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).
- b. Pulse width \leq 300 µs; duty cycle \leq 2 %.
- c. Current limited by the package (die current = 51 A).



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Fig. 1 - Typical Output Characteristics





Fig. 2 - Typical Output Characteristics



VGS, Gate-to-Source Voltage (volts) Fig. 3 - Typical Transfer Characteristics




Fig. 4 - Normalized On-Resistance vs. Temperature







Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage



V_{SD}, Source-to-Drain Voltage (volts)

Fig. 7 - Typical Source-Drain Diode Forward Voltage




Fig. 6 - Typical Gate Charge vs. Gate-to-Source Voltage




Fig. 8 - Maximum Safe Operating Area








Fig. 9 - Maximum Drain Current vs. Case Temperature




Fig. 10a - Switching Time Test Circuit




Fig. 10b - Switching Time Waveforms






Fig. 11 - Maximum Effective Transient Thermal Impedance, Junction-to-Case







 V_{DS}

Fig. 12a - Unclamped Inductive Test Circuit

Fig. 12b - Unclamped Inductive Waveforms




Fig. 12c - Maximum Avalanche Energy vs. Drain Current




Fig. 13a - Basic Gate Charge Waveform





Fig. 13b - Gate Charge Test Circuit





Peak Diode Recovery dV/dt Test Circuit







Fig. 14 - For N-Channel

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?91292.





TO-220AB



	MILLIMETERS		INC	HES		
DIM.	MIN.	MAX.	MIN.	MAX.		
Α	4.25	4.65	0.167	0.183		
b	0.69	1.01	0.027	0.040		
b(1)	1.20	1.73	0.047	0.068		
С	0.36	0.61	0.014	0.024		
D	14.85	15.49	0.585	0.610		
Е	10.04	10.51	0.395	0.414		
е	2.41	2.67	0.095	0.105		
e(1)	4.88	5.28	0.192	0.208		
F	1.14	1.40	0.045	0.055		
H(1)	6.09	6.48	0.240	0.255		
J(1)	2.41	2.92	0.095	0.115		
L	13.35	14.02	0.526	0.552		
L(1)	3.32	3.82	0.131	0.150		
ØΡ	3.54	3.94	0.139	0.155		
Q	2.60	3.00	0.102	0.118		
ECN: X10-0416-Rev. M, 01-Nov-10						

DWG: 5471

 $^{^{\}star}$ M = 1.32 mm to 1.62 mm (dimension including protrusion) Heatsink hole for HVM





Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Document Number: 91000 www.vishay.com Revision: 11-Mar-11