HF7FD

SUBMINIATURE HIGH POWER RELAY



File No.:E134517



File No.: 40008374



File No.:CQC09002037921



Features

- 12A switching capability
- Ambient temperature meets 105°C
- High performance, Low profile
- Product in accordance to IEC 60335-1 available
- 2kV dielectric strength (between coil and contacts)
- UL94, V-0, CTI250 flammability class
- Double pins type available
- 1 Form A and 1 Form C configurations
- UL insulation system: Class F available
- Environmental friendly product (RoHS compliant)
- Outline Dimensions: (22.0 x 16.0 x 16.4) mm

CO	NIT	ГΛ	CI	ם ד	Λ	ГΛ
	1.71				/=\	\blacksquare

Contact arrangement		1A	1C	
Contact resistance		100mΩ max.(at 1A 24VDC		
Contact material			AgSnO2, AgCdO	
Contact rating (Res. load)		A 250VAC	12A 125VAC	
		A 250VAC	NO: 10A 250VAC	
	10A 250VAC		NC: 7A 250VAC	
Max. switching voltage	250VAC / 28VDC			
Max. switching current	16A		10A	
Max. switching power	400	0VA / 280W	2500VA / 196W	
Mechanical endurance			1 x 10 ⁷ ops	
	1A	Flux proof	fed / Plastic sealed:	
Electrical endurance			1 x 10 ⁵ ops	
(See approval reports for more details)		Flux	proofed: 5x 10 ⁴ ops	
more detaile,	1C	Plastic sealed: NO: 5 x 10 ⁴ ops		
			NC: 1 x 10 ⁴ ops	

CHARACTERISTICS

Insulation	resistanc	е	100MΩ (at 500VDC)	
Dielectric	Between coil & contacts		2000VAC 1min	
strength	Between	n open contacts	750VAC 1min	
Operate tii	me (at no	mi. volt.)	10ms max.	
Release ti	me (at no	omi. volt.)	5ms max.	
Humidity			5% to 85% RH	
Shock resistance		Functional	98m/s ²	
		Destructive	980m/s ²	
A b : t - t -			HF7FD: -40°C to 85°C	
Ambient temperature			HF7FD-T: -40°C to 105°C	
Vibration r	esistance)	10Hz to 55Hz 1.5mm DA	
Termination	n		PCB	
Unit weigh	ıt		Approx. 14g	
C			Plastic sealed,	
Construction			Flux proofed	

Notes: 1) The data shown above are initial values.

- 2) Please find coil temperature curve in the characteristic curves below.
- 3) UL insulation system: Class F, Class B.

COIL

Coil power Approx. 360mW

COIL	DATA	at 23°C
COIL	DAIA	ar /3 C

COIL DATA				at 23 C
Nominal Voltage VDC	Pick-up Voltage VDC max.	Drop-out Voltage VDC min.	Max. Allowable Voltage VDC	Coil Resistance Ω
3	2.25	0.3	3.9	25 x (1±10%)
5	3.75	0.5	6.5	70 x (1±10%)
6	4.50	0.6	7.8	100 x (1±10%)
9	6.75	0.9	11.7	225 x (1±10%)
12	9.00	1.2	15.6	400 x (1±10%)
18	13.5	1.8	23.4	900 x (1±10%)
24	18.0	2.4	31.2	1600 x (1±15%)
48	36.0	4.8	62.4	6400 x (1±15%)

SAFETY APPROVAL RATINGS

	1 Form A	HF7FD	12A 250VAC (at 85°C, AgSnO ₂ , Double pin) 10A 277VAC 10A 28VDC	
UL/CUL		HF7FD-T (AgSnO ₂)	16A 250VAC (at 40°C) 10A 250VAC (at 105°C) 8A 250VAC (at 105°C) 1/2HP 125VAC (at 40°C) 1/2HP 250VAC (at 40°C)	
	1 Form C	12A 125VAC 7A 277VAC 7A 28VDC		
VDE	1 Form A	12A 250VAC (AgSnO ₂ , Double pin 10A 250VAC		
	1 Form C	7A 250VAC		


Notes: Only some typical ratings are listed above. If more details are required, please contact us.



HONGFA RELAY

ISO9001, ISO/TS16949, ISO14001, OHSAS18001, IECQ QC 080000 CERTIFIED

2012 Rev. 1.01



Notes: 1) Under the ambience with dangerous gas like H₂S, SO₂ or NO₂, plastic sealed type is recommended; Please test the relay in real applications. If the ambience allows, flux proofed type is preferentially recommended.

If water cleaning is required after the relay is assembled on PCB, please contact us for suggestion about suitable parts.

2) If plastic sealed type is selected for cleaning purpose, the vent-hole cover should be excised after cleaning.

OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT


Unit: mm


Outline Dimensions


PCB Layout (Bottom view)

Wiring Diagram (Bottom View)


1 Form A (Single pin type)









1 Form C (Single pin type)







OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT


Unit: mm


Outline Dimensions


PCB Layout (Bottom view)

Wiring Diagram (Bottom View)


1 Form A (Double pins type)









1 Form C (Double pins type)








Remark: 1) In case of no tolerance shown in outline dimension: outline dimension ≤1mm, tolerance should be ±0.2mm; outline dimension >1mm and ≤5mm, tolerance should be ±0.3mm; outline dimension >5mm, tolerance should be ±0.4mm.

2) The tolerance without indicating for PCB layout is always ±0.1mm.


CHARACTERISTIC CURVES

MAXIMUM SWITCHING POWER



COIL TEMPERATURE RISE

6- Ø1.4



Disclaimer

This datasheet is for the customers' reference. All the specifications are subject to change without notice.

We could not evaluate all the performance and all the parameters for every possible application. Thus the user should be in a right position to choose the suitable product for their own application. If there is any query, please contact Hongfa for the technical service. However, it is the user's responsibility to determine which product should be used only.

© Xiamen Hongfa Electroacoustic Co., Ltd. All rights of Hongfa are reserved.