

## 3-point internal measuring probe set with dial gauge Marator 1086 R

Micromar 844 A



### Application:

For measuring through-bores and blind bores and short centring shoulders in series production.

### Execution:

- Self-centring and self-aligning
- Carbide-tipped measuring faces
- Interchangeable measuring heads

### Delivery:

1 measuring element, measuring heads with setting rings, operating instructions, Marator 1086 R dial gauge



<b>Art. no.</b>	<b>31913 640</b>
<b>Brand</b>	MAHR
<b>Manufacturer Part Number</b>	4487763
<b>Min./max. length measuring range</b>	50-100 mm
<b>Error limit</b>	5 µm
<b>Data transmission type</b>	USB
<b>Digit increment</b>	0.0005 mm
<b>Model</b>	844 AS
<b>IP protection class</b>	IP 42
<b>Number of measurement heads</b>	4 PCS
<b>Adjusting ring diameter</b>	60 mm, 85 mm
<b>Preset function</b>	Yes
<b>With ABS function</b>	Yes
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	3V CR2032 Lithium
<b>Included in delivery</b>	MarCator 1086 R, operating instructions, adjusting rings. Key for changing measuring heads (from 30 mm), hexagon key, case
<b>Gross Weight</b>	6.125 kg
<b>Product Group</b>	305

### EAN

4059192021641