

1-2199298-2 ✓ ACTIVE

## DIPLOMATE

TE Internal #: 1-2199298-2

DIP Sockets, Stamped & Formed, 8 Position, Low Connector

Profile, Row-to-Row Spacing .3 in [7.62 mm], Vertical, Straight, Tin

[View on TE.com >](#)



Connectors > Socket Connectors > IC Sockets > DIP Sockets > DIP Socket: Low Profile, Stamped & Formed, Open, Tin



Contact Fabrication: **Stamped & Formed**

Number of Positions: **8**

Connector Profile: **Low**

Row-to-Row Spacing: **7.62 mm [ .3 in ]**

PCB Mount Orientation: **Vertical**

[All DIP Socket: Low Profile, Stamped & Formed, Open, Tin \(6\)](#)

## Features

### Product Type Features

Leg Style	Straight
Connector & Contact Terminates To	Printed Circuit Board
Product Type	Socket

### Configuration Features

Number of Positions	8
PCB Mount Orientation	Vertical
Number of Rows	2

### Electrical Characteristics

Contact Resistance	20 mΩ
Insulation Resistance	1000 MΩ

### Body Features

Sleeve Material	Brass/Copper
Sleeve Plating Material	Tin/Lead
Frame Style	Ladder
Connector Profile	Low
Color	Black



### Contact Features

Socket Style	Standard
Mating Contact Type	Dual Leaf
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Fabrication	Stamped & Formed
Contact Mating Area Plating Material	Tin
	60 μin
Contact Current Rating (Max)	1 A
Socket Type	DIP
Contact Type	Pin

### Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
	3 in

### Mechanical Attachment

Connector Mounting Type	Board Mount
Mating Alignment Type	Polarization
Mating Alignment	With

### Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
Housing Material	PBT GF30

### Dimensions

Height Above PC Board	5.1 mm[.2 in]
Row-to-Row Spacing	7.62 mm[.3 in]
	.4 in

### Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features



Tubes per Box	2
Packaging Method	Box & Tube
Packaging Quantity	60

#### Other

Quantity per Tube	6000
-------------------	------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 5787617-3  
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,



TE Part # 5787617-4  
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,



TE Part # 5787745-5  
USB A R/A STAK ASSY THRU HOLE



TE Part # 5787745-1  
USB A R/A STAK ASSY THRU HOLE



TE Part # 5787617-8  
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,



TE Part # 5787745-2  
USB A R/A STAK ASSY THRU HOLE



TE Part # 5787745-4  
USB A R/A STAK ASSY THRU HOLE



TE Part # 5787617-1  
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,



TE Part # 5787617-2  
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,



TE Part # 292323-6  
REC ASSY RIGHT ANGLE STACKED THRUHOLE US



TE Part # 5787617-5  
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,



TE Part # 5787617-6  
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,



TE Part # 5787745-3  
USB A R/A STAK ASSY THRU HOLE



TE Part # 292323-5  
RECEPTACLE ASSY RIGHT ANGLE STACKED THRU




TE Part # 292323-1  
REC ASSY RIGHT ANGLE STACKED THRUHOLE US


### Customers Also Bought




TE Part #1-2199298-6  
DIP Socket: Low Profile, Stamped & Formed, Open, Tin



TE Part #NB07226001  
Single Wall RNF-100 Reel HS Tubing



TE Part #1-2199298-8  
24P,DIP SKT,300 CL,LDR,PB FREE



TE Part #1-2199298-1  
6P,DIP SKT,300 CL,LDR,PB FREE



## Documents

### Product Drawings

8P,DIP SKT,300 CL,LDR,PB FREE

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2199298-2\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2199298-2\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2199298-2\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[DIP Sockets Quick Reference Guide \(EN\)](#)

English

### Product Environmental Compliance

[MD\\_1-2199298-2\\_03262018237\\_dmtec](#)

English

[MD\\_1-2199298-2\\_03262018237\\_dmtec](#)

English