

Crimp contact - CDC-MP 0,14-0,5 - 1016664


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact



Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 055626 499017
GTIN	4055626499017

Technical data

Dimensions for the product

Pitch	0 mm
-------	------

Packaging information

Type of packaging	Bulk goods
Pieces per package	100
Denomination packing units	Pcs.

General product information

Type of note	Note on application
	Note regarding documentation
Note	The crimp contacts may only be processed with approved crimping tools.
	The crimp heights depend on the crimping tool used. You can find the values in the tool documentation.

Accessories

Accessories

Crimp contact - CDC-MP 0,14-0,5 - 1016664

Accessories

Crimping tool

Crimping pliers - CRIMPFOX-P CDC 0.5L - 1142831



Crimping tool, for COMBICON crimp connectors, cross section: 0.14 ... 0.50 mm², unlockable pressure lock, precise parallel crimping, front entry, incl. positioning tool

Additional products

PCB direct plug - CDDC 1,5/ 2-PV-3,5 - 1016515



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 2, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

PCB direct plug - CDDC 1,5/ 3-PV-3,5 - 1016513



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 3, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

PCB direct plug - CDDC 1,5/ 4-PV-3,5 - 1016512



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 4, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

PCB direct plug - CDDC 1,5/ 5-PV-3,5 - 1016516



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 5, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

Crimp contact - CDC-MP 0,14-0,5 - 1016664

Accessories

PCB direct plug - CDDC 1,5/ 6-PV-3,5 - 1016517



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 6, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

PCB direct plug - CDDC 1,5/ 7-PV-3,5 - 1016518



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 7, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

PCB direct plug - CDDC 1,5/ 8-PV-3,5 - 1016519



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 8, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

PCB direct plug - CDDC 1,5/ 9-PV-3,5 - 1016520



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 9, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

PCB direct plug - CDDC 1,5/10-PV-3,5 - 1016521



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 10, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

Crimp contact - CDC-MP 0,14-0,5 - 1016664

Accessories

PCB direct plug - CDDC 1,5/11-PV-3,5 - 1016510



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 11, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

PCB direct plug - CDDC 1,5/12-PV-3,5 - 1016522



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 12, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

PCB direct plug - CDDC 1,5/13-PV-3,5 - 1016523



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 13, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

PCB direct plug - CDDC 1,5/14-PV-3,5 - 1016524



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 14, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

PCB direct plug - CDDC 1,5/15-PV-3,5 - 1016525



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 15, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

Crimp contact - CDC-MP 0,14-0,5 - 1016664

Accessories

PCB direct plug - CDDC 1,5/16-PV-3,5 - 1016526



PCB direct plug, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 16, pitch: 3.5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

Direct connector - CDDC 2,5/ 2-PV-5,0 - 1016293



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 2, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

Direct connector - CDDC 2,5/ 3-PV-5,0 - 1016292



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 3, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

Direct connector - CDDC 2,5/ 4-PV-5,0 - 1016290



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 4, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

Direct connector - CDDC 2,5/ 5-PV-5,0 - 1016289



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 5, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

Crimp contact - CDC-MP 0,14-0,5 - 1016664

Accessories

Direct connector - CDDC 2,5/ 6-PV-5,0 - 1016288



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 6, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD
- Direct plug-in technology, pin layout: Linear pinning

Direct connector - CDDC 2,5/ 7-PV-5,0 - 1016286



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 7, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD
- Direct plug-in technology, pin layout: Linear pinning

Direct connector - CDDC 2,5/ 8-PV-5,0 - 1016285



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 8, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD
- Direct plug-in technology

Direct connector - CDDC 2,5/ 9-PV-5,0 - 1016280



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 9, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD
- Direct plug-in technology

PCB direct plug - CDDC 2,5/10-PV-5,0 - 1016279




PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 10, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

Crimp contact - CDC-MP 0,14-0,5 - 1016664

Accessories

PCB direct plug - CDDC 2,5/11-PV-5,0 - 1016278



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 11, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

PCB direct plug - CDDC 2,5/12-PV-5,0 - 1016277



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 12, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

PCB direct plug - CDDC 2,5/13-PV-5,0 - 1016276



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 13, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

PCB direct plug - CDDC 2,5/14-PV-5,0 - 1016274



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 14, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

PCB direct plug - CDDC 2,5/15-PV-5,0 - 1016273



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 15, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

Crimp contact - CDC-MP 0,14-0,5 - 1016664

Accessories

PCB direct plug - CDDC 2,5/16-PV-5,0 - 1016272



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 16, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT ROMANIA
Splaiul Unirii 165 Timpuri Noi Square TNO1, Etaj 1
Bucuresti 030133
Romania
+40 21 350 88 12 - 3
+40 37 448 56 32 - 7
<http://www.phoenixcontact.ro>