



CIRCUIT BREAKER 10KA, 3POLE, C, 15A ACC. TO UL 489 - 480Y/277V

Figure similar

General technical data		
Number of poles		3
Number of poles / Note		3P
Tripping characteristic class		C
Installation environment regarding EMC		Suitable for environment B (immunity to interference not applicable)
circuit-breaker / Design		5SJ4
Mechanical service life (switching cycles) / typical		20 000
Equipment marking / acc. to DIN 40719 extended according to IEC 204-2 / acc. to IEC 750		F
Overvoltage category		3
Voltage		
Insulation voltage / with AC / Rated value	V	440
Supply voltage		
Supply voltage frequency / Rated value	Hz	50
Protection class		
Protection class IP		IP20, with connected conductors, IP 40 in the handle range
Switching capacity		
Switching capacity current		
• acc. to EN 60898 / Rated value	kA	10
• acc. to IEC 60947-2 / Rated value	kA	15
Dissipation		
Active power loss		

- for rated value of the current / with AC / in hot operating state / per pole

W	1.8
---	-----

### Electricity

rated current $I_n$ / IEC, DIN/VDE / at 40 Cel	A	15
Current / with AC / Rated value	A	15

### Main circuit

<b>Operating voltage</b>		
• minimum	V	24
• with AC / acc. to UL 489 and CSA C22.2 No. 5-02 / maximum	V	277
• for DC / 1-channel / acc. to UL 489 and CSA C22.2 No. 5-02 / maximum	V	60
• for DC / 2-channel / acc. to UL 489 and CSA C22.2 No. 5-02 / maximum	V	125
• for DC / Rated value / maximum	V	60

### Product details

Product feature / Touch protection		Yes
<b>Product component</b>		
• Tunnel terminals top		No
• Tunnel terminals bottom		No
• combined terminal top		Yes
• combined terminal bottom		Yes
<b>Product property</b>		
• halogen-free		Yes
• sealable		Yes
• silicon-free		Yes
Product expansion / can be installed / supplementary devices		Yes

### Product function

<b>Product function</b>		
• Note		Terminal tightening torque for Cu, 60/75°C; 3.5Nm/31lb.in
• neutral conductor switching		No

### Short circuit

Breaking capacity short-circuit current ( $I_{cn}$ ) / with AC / acc. to UL 1077 and CSA C22.2 No.235	kA	10
---	----	----

### Number

Number of test cycles / for environmental testing / acc. to IEC 60068-2-30		6
--	--	---

### Connections

Connectable conductor cross-section / finely stranded / with core end processing		
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	mm <sup>2</sup>	0.75
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	mm <sup>2</sup>	25
Position / of power supply cord		Any

### Mechanical Design

Height	mm	121
Width	mm	54
Depth	mm	76
mounting position		any
Installation depth	mm	70
Number of width units		3
Mounting type		on standard mounting rail

### Environmental conditions

Influence of the surrounding temperature		max. 95% humidity
Vibration resistance		50 m/s <sup>2</sup> at 25 to 150Hz and 60m/s <sup>2</sup> at 35Hz (4sec)
Vibration resistance / acc. to IEC 60068-2-6		50 m/s <sup>2</sup> at 25 to 150Hz and 60m/s <sup>2</sup> at 35Hz (4sec)
Ambient temperature		
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	°C	-25
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	°C	55
<ul style="list-style-type: none"> <li>• during storage / minimum</li> </ul>	°C	-40
<ul style="list-style-type: none"> <li>• during storage / maximum</li> </ul>	°C	75

### Certificates

Equipment marking		
<ul style="list-style-type: none"> <li>• acc. to DIN EN 61346-2</li> </ul>		F
<ul style="list-style-type: none"> <li>• acc. to DIN EN 81346-2</li> </ul>		F

### General Product Approval



### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SJ43187HG42>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/5SJ43187HG42/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SJ43187HG42](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SJ43187HG42)

**CAX-Online-Generator**


<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>



**last modified:**



**11.03.2015**