2 Pad Ceramic Package, 3.2mm x 1.5mm



IL3X2 Series

Product Features:

±10ppm Tolerance Available SMD Package Low Profile RoHS and REACH Compliant


Applications:

Real Time Clock Source Metering Industrial Control Time Reference

Electrical Specifications

Frequency	32.768kHz	
Equivalent Series Resistance	70 kOhms Maximum	
Shunt Capacitance (C0)	0.95pF Typical, 2.0pF Maximum	
Frequency Tolerance (at 25°C)	±10ppm or ±20ppm	
Frequency Stability (over Temperature)	-0.034ppm/(Change in °C)² Typical	
Turn over Temperature	25°C ±5°C	
Mode of Operation	Fundamental	
Crystal Cut	X-Cut (Tuning Fork)	
Load Capacitance	6pF, 7pF, 9pF, 12.5pF or Specify	
Drive Level	1μWatt Maximum	
Aging	±3ppm/Year Maximum	
Operating Temperature Range	-40°C to +85°C	
Storage Temperature Range	-40°C to +85°C	

Mechanical and Solder Pad Dimensions



All Dimensions in Millimeters

Part Number Guide


Sample Part Number: IL3X2 - HX5F12.5 - 32.768 kHz						
Package	Frequency Tolerance	Frequency Stability	Operating Temperature Range	Mode of Operations	Load Capacitance	Frequency
IL3X2-	J = ±10ppm H = ±20ppm	X = X Cut	5 = -40°C to +85°C	F = Fundamental	6 = 6pF 7 = 7pF 9 = 9pF 12.5 = 12.5pF	- 32.768 kHz

Rev: 07/23/19_A





Pb Free Solder Reflow Profile:



Units are backward compatible with +240°C reflow process
--

Ts max to T _L (Ramp-up Rate)	3°C / second max
Preheat	
Temperature min (Ts min)	150°C
Temperature typ (Ts typ)	175°C
Temperature max (Ts max)	200ºC
Time (Ts)	60 to180 seconds
Ramp-up Tate (T _L to Tp	3°C / second max
Time Maintained Above	
Temperature (T _L)	217ºC
Time (T _{L)}	60 to 150 seconds
Dook Tomporeture (Tp)	260°C max for 10
Peak Temperature (Tp)	seconds
Time within 5°C to Peak	20 to 40 seconds
Temperature (Tp)	20 to 40 Seconds
Ramp-down Rate	6°C / second max
Tune 25°C to Peak Temperature	8 minutes max


Package Information:

MSL = 1 (package does not contain plastic, storage life is unlimited under normal room conditions) Termination = e4 (Au over Ni over W base metallization)

Termination = e4 (Au over Ni over W base metallizati Cover: Metal

Seam Seal

Tape and Reel Information:



Environmental Specifications:

Thermal Shock	MIL-STD-883, Method 1011, Condition A
Moisture Resistance	MIL-STD-883, Method 1004
Mechanical Shock	MIL-STD-883, Method 2002, Condition B
Mechanical Vibration	MIL-STD-883, Method 2007, Condition A
Resistance to Soldering Heat	J-STD-020C, Table 5-2 Pb-free devices (except 2 cycles max)
Hazardous Substance	Pb-Free / RoHS / Green Compliant
Solderability	JESD22-B102-D Method 2 (Preconditioning E)
Gross Leak	MIL-STD-883, Method 1014, Condition C
Fine Leak	MIL-STD-883, Method 1014, Condition A2, R1=2x10-8 atm cc/s
Solvent Resistance	MIL-STD-202, Method 215

Marking:

Line 1: Manufacturer Designator, Date Code

Rev: 07/23/19_A