


Time-Lag Subminiature Fuse Radial Leaded

multicomp PRO

**RoHS
Compliant**



Description

The product provides protection for printed circuit boards used in a large variety of applications that need fuses with time-delay, low breaking capacity. The sub-miniature device is constructed of a plastic cap and base with a tin plated copper lead wire. It offers excellent mounting characteristics and is 100% tested for cold resistance.

Applications

Its main applications are for consumer electronics, LED drivers, power supplies, battery chargers and controllers for industrial use.

Features

- Subminiature fuse with time delay, low breaking capacity
- Small, rectangular and leaded design minimizes board space and eliminates the need for additional mounting components
- Plastic cap / brown thermoplastic fuse body
- 0.6mm lead wires made of tin plated copper.
- Protection against harmful over-currents in primary and secondary applications
- Lead-free and Halogen-free
- Designed according to IEC 60127

Specifications

Operating Temperature	: -55°C to +125°C
Storage Conditions	: +10°C to +60°C
Relative Humidity	: ≤ 75% yearly average without dew, maximum 30 days at 95%
Vibration Resistance	: 24 cycles at 15 min. each 10-60Hz at 0.75mm amplitude 60-2000Hz at 10g acceleration


Electrical Characteristics

Part Number	Amp Code	Rated Current	Max. Voltage	Max. Voltage Drop (mV)	Max. Power Dissipation (mW)	Nominal Melting I ² t (A ² sec)	Breaking Capacity
MP001613	1100	1A	400V AC	140	500	6.7	100A @ 125V AC 100A @ 250V AC 50A or 10In @ 300V AC 160A @ 125V/250V AC 100A @ 277V/300V/400V AC

Note:

1. Permissible continuous operating current is ≤100% at ambient temperature of 23°C (73.4°F)
2. The current values used for calculating I²T should be within the standard range of 8ms ~ 10ms.

Temperature Derating Curve



$$\text{Calculation for ideal fuse selection} = \frac{\text{Operating Current (A)}}{\text{Rating (\%} \times 0.75)}$$

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro


multicomp PRO

Time-Lag Subminiature Fuse Radial Leaded

Time vs Current Characteristics Table

Time vs Current Characteristics: UL-248-14					
Rated Current	150%	210%	275%	400%	1000%
1A	>1h	<2min	400ms-10s	150ms-3s	20ms-150ms


Soldering Parameters




260°C = ≤5 sec (Wave Soldering)
 350°C = ≤3 sec (Hand Soldering)
 Soldering Peak:
 260°C = 10 sec (IEC 60068-20)

Construction and Mechanical Characteristics

Construction (cross section)



Diagram




Dimensions : Millimetres

Time-Lag Subminiature Fuse Radial Leaded



Packing Information



Part Number Table

Description	Part Number
Subminiature Fuse, Time-Lag, 1A, 400V AC, Radial Leaded	MP001613

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

