

High-feed milling cutters with thread

For indexable milling inserts XDM. 0903..

ATORN®

Version

- For indexable milling inserts XDMW / XDMT 0903..
- Wear-resistant, nickel-plated version with internal cooling
- Tightening torque for clamping screw indexable insert 1.2 Nm (TX 08)

Advantage

- Broad range of applications
- Minimum-vibration milling even for long mounting lengths
- Optimum roughing tool
- Tooth feed possible up to 3 mm
- Reduces production times



Art. No.	16026 406
Max. cutting edge diameter	20 mm
Min. cutting edge diameter	11 mm
Clearance length	30 mm
Thread dimension	M10
Radius, theoretical	1.3 mm
max. ap	1 mm
Number of cutting edges	4 PCS

EAN-Code

4050293422429