

Hydraulic expansion chuck

In accordance with ISO 12164 (DIN 69893)



Application:

For clamping drill bits and milling tools with straight shank.

Execution:

- Longer service life of cutting tools.
- Capable of clamping all common shank types.
- With axial length adjustment (max. V in the drawing).

Advantage:

- High-precision centric clamping.
- High torque transfer.
- Good surface qualities.
- Suitable for high rotation speeds.
- Excellent vibration-damping properties.

Delivery:

1x hydraulic expansion chuck in accordance with ISO 12164 (DIN 69893).



Art. no.	23735 052
Brand	SCHUNK
Manufacturer Part Number	0204053
Tool holding device	HSK 63
Construction length	Slim
Clamping diameter	10 mm
Form	A
Projecting length	80 mm
Tapered diameter	30 mm
Outer diameter	50 mm
Clear length	35 mm
Clamp in depth	41 mm
Suitable for thread	M8 x 1
Max. adjustment travel	10 mm
Coolant supply	Internal axial
Balancing quality	G 2.5 at 25 rpm
Gross Weight	1.070 kg
Product Group	229