

### Features

- ◆ Ultra wide 4:1 input voltage range
- ◆ Internal EMI-filter meets EN 55022, class A without external components
- ◆ High efficiency up to 87%
- ◆ Operating temperature range -40°C to +85°C
- ◆ No minimum load required
- ◆ I/O isolation 1'500 VDC
- ◆ Overload protection
- ◆ 3-year product warranty



The THD 10WIN series is designed for an optimized cost/performance ratio of DC/DC converters with output power of 10 Watt.

They come with an internal EMI-filter to meet EN55022, class A without external components. General features like no minimum load requirement, overload protection and high efficiency make these converters easy to design in. With the popular DIP-24 standard package they are also a drop in replacement for many cost critical applications.

### Models

| Order code     | Input voltage range             | Output voltage | Output current max. | Efficiency typ. |
|----------------|---------------------------------|----------------|---------------------|-----------------|
| THD 10-2410WIN | 9 – 36 VDC<br>(24 VDC nominal)  | 3.3 VDC        | 2700 mA             | 86 %            |
| THD 10-2411WIN |                                 | 5.1 VDC        | 2000 mA             | 85 %            |
| THD 10-2412WIN |                                 | 12 VDC         | 833 mA              | 87 %            |
| THD 10-2413WIN |                                 | 15 VDC         | 666 mA              | 87 %            |
| THD 10-2415WIN |                                 | 24 VDC         | 416 mA              | 87 %            |
| THD 10-2422WIN |                                 | ±12 VDC        | ±416 mA             | 87 %            |
| THD 10-2423WIN |                                 | ±15 VDC        | ±333 mA             | 87 %            |
| THD 10-4810WIN | 18 – 75 VDC<br>(48 VDC nominal) | 3.3 VDC        | 2700 mA             | 86 %            |
| THD 10-4811WIN |                                 | 5.1 VDC        | 2000 mA             | 85 %            |
| THD 10-4812WIN |                                 | 12 VDC         | 833 mA              | 87 %            |
| THD 10-4813WIN |                                 | 15 VDC         | 666 mA              | 87 %            |
| THD 10-4815WIN |                                 | 24 VDC         | 416 mA              | 87 %            |
| THD 10-4822WIN |                                 | ±12 VDC        | ±416 mA             | 87 %            |
| THD 10-4823WIN |                                 | ±15 VDC        | ±333 mA             | 87 %            |

### Input Specifications

|  |  |
|--|--|
| Input current at no load                   | 24 Vin models: 30 mA typ.<br>48 Vin models: 20 mA typ.   |
| Recommended input fuse (slow blow)         | 24 Vin models: 2000 mA<br>48 Vin models: 1000 mA   |
| Start-up voltage / under voltage shut down | 24 Vin models: 9 VDC / 8.5 VDC (or lower)<br>48 Vin models: 18 VDC / 17 VDC (or lower)   |
| Surge voltage (1 sec. max.)                | 24 Vin models: 50 V max.<br>48 Vin models: 100 V max.  |
| Conducted noise                            | EN 55022 class A without external components   |
| ESD (electrostatic discharge)              | EN 61000-4-2, air $\pm 8$ kV, contact $\pm 6$ kV, perf. criteria A   |
| Radiated immunity                          | EN 61000-4-3, 10 V/m, perf. criteria A   |
| Fast transient / surge                     | EN 61000-4-4, $\pm 2$ kV, perf. criteria A<br>EN 61000-4-5, $\pm 1$ kV perf. criteria A<br>with external capacitor chemi-con KY 220 $\mu$ F, 100 V |
| Conducted immunity                         | EN 61000-4-6, 10 Vrms, perf. criteria A  |

### Output Specifications

|   |  |
|---|--|
| Voltage set accuracy                                | $\pm 2$ % max.   |
| Regulation  | – Input variation Vin min. to Vin max. 1.0 % max.<br>– Load variation 0 – 100 % single output models: 1.2 % max.<br>dual output models balanced load: 2.0 % max.   |
| Minimum load  | not required   |
| Temperature coefficient                             | $\pm 0.02$ %/K   |
| Ripple and noise (20 MHz Bandwidth)                 | 100 mVp-p max.   |
| Transient recovery time (25% load step change)      | 300 $\mu$ S response time typ.   |
| Transient response deviation (25% load step change) | $\pm 5$ % max.   |
| Current limitation                                  | 110–150 % of Iout hiccup, automatic recovery   |
| Short circuit protection                            | hiccup, automatic recovery   |
| Over load protection                                | 150 % of Iout max. typ.  |
| Capacitive load                                     | 3.3 & 5.1 VDC models: 1000 $\mu$ F max.<br>12 VDC models: 470 $\mu$ F max.<br>15 VDC models: 330 $\mu$ F max.<br>24 VDC models: 150 $\mu$ F max.<br>$\pm 12$ VDC models: 220 $\mu$ F max. (each output)<br>$\pm 15$ VDC models: 150 $\mu$ F max. (each output) |

### General Specifications

|   |   |
|---|---|
| Temperature ranges  | – Operating (natural convection 20 LFM) –40°C to +85°C<br>– Case temperature +105°C max.<br>– Storage –50°C to +125°C |
| Derating  | 3.3 %/K above +70°C   |
| Humidity (non condensing)   | 95 % rel H max.   |
| Reliability, calculated MTBF (MIL-HDBK-217F, at +25°C, ground benign) | 1'000'000 h   |
| Isolation voltage (input/output 60 sec., rated)                       | 1'500 VDC   |
| Isolation capacitance (input/output, 100 KHz, 1 V)                    | 1'000 pF typ.   |
| Isolation resistance (input/output, 500 VDC)                          | >1'000 M Ohm  |

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

**General Specifications**


|                          |   |
|--------------------------|---|
| Remote On/Off            | <ul style="list-style-type: none"> <li>- On: 3.5 ... 12 VDC or open circuit</li> <li>- Off: 0 ... +1.2 VDC or short circuit pin 1 and pin 2</li> <li>- Off idle current: 10 mA max.</li> </ul>  |
| Switching frequency      | 330 kHz typ.  |
| Safety standards         | UL/cUL 60950-1, IEC/EN 60950-1  |
| Safety approvals         | <ul style="list-style-type: none"> <li>- CSA certificate of compliance</li> <li>- CB test certificate</li> <li>- Certification documents</li> </ul> <p>CAN/CSA-C22.2 No 60950-1-07, Am 1:2011<br/>ANSI/UL Std No 60950-1, 2nd Ed, AM 1:2011<br/>IEC 60950-1:2005 2nd Ed, Am 1:2009<br/><a href="http://www.tracopower.com/overview/thd10win">www.tracopower.com/overview/thd10win</a></p> |
| Environmental compliance | <ul style="list-style-type: none"> <li>- Reach</li> <li>- RoHS</li> </ul> <p><a href="http://www.tracopower.com/products/reach-declaration.pdf">www.tracopower.com/products/reach-declaration.pdf</a><br/>RoHS directive 2011/65/EU</p>   |

**Physical Specifications**

|   |   |
|---|---|
| Casing  | metal with non conductive baseplate           |
| Pin   | copper alloy with gold plated nickel subplate |
| Weight  | 17.3 g (0.61 oz)                              |
| Soldering temperature (1.5mm from case for 10 sec.) | max. 260°C                                    |

**Application note:** [www.tracopower.com/products/thd10win-application.pdf](http://www.tracopower.com/products/thd10win-application.pdf)

**Outline Dimensions**



| Pin-Out |               |               |
|---------|---------------|---------------|
| Pin     | Single        | Dual          |
| 1       | Remote On/Off | Remote On/Off |
| 2       | -Vin (GND)    | -Vin (GND)    |
| 3       | -Vin (GND)    | -Vin (GND)    |
| 9       | No pin        | Common        |
| 11      | No function   | -Vout         |
| 14      | +Vout         | +Vout         |
| 16      | -Vout         | Common        |
| 22      | +Vin (Vcc)    | +Vin (Vcc)    |
| 23      | +Vin (Vcc)    | +Vin (Vcc)    |

Dimensions in [mm], ( ) = Inch  
 Pin diameter  $\varnothing 0.5 \pm 0.05$  (0.02  $\pm$  0.002)  
 Tolerances  $\pm 0.5$  ( $\pm 0.02$ )  
 Pin pitch tolerances  $\pm 0.25$  ( $\pm 0.01$ )

Specifications can be changed without notice! Make sure you are using the latest documentation, downloadable at [www.tracopower.com](http://www.tracopower.com)