

284858-1 ✓ ACTIVE

AMP | AMP MCP 1.5K, AMP MCP 2.8, AMP MCP Connector System

TE Internal #: 284858-1

Hybrid, Housing for Male Terminals, Wire-to-Wire, 12 Position, 4.2 mm / 4.65mm [.183in / .165in] Centerline, Black, Signal

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Housings > AMP MCP, SEALED CONNECTOR HOUSING



Connector & Housing Type: **Housing for Male Terminals**

Mating Tab Width: **1.6 mm, 2.8 mm** [.063 in, .11 in]

Connector System: **Wire-to-Wire**

Number of Positions: **12**

Centerline (Pitch): **4.2 mm, 4.65 mm** [.165 in, .183 in]

[All AMP MCP, SEALED CONNECTOR HOUSING \(159\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Wire
Sealable	No
Hybrid Connector	No
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	12
Number of Rows	2

Electrical Characteristics

Operating Voltage	24 VDC
Nominal Voltage Architecture	12 V, 24 V

Body Features

Cable Exit Angle	180°
Body Material	PA GF
Primary Product Color	Black

Contact Features

Mating Tab Width	1.6 mm, 2.8 mm [.063 in][.11 in]
------------------	----------------------------------



Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	Yes
Strain Relief	No

Housing Features

Centerline (Pitch)	4.2 mm, 4.65 mm [.165 in][.183 in]
--------------------	------------------------------------

Dimensions

Product Width	20.8 mm [.819 in]
Product Length	34.3 mm [1.35 in]
Product Height	38.7 mm [1.524 in]
Row-to-Row Spacing	3.4 mm [.134 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C [158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F]
Operating Temperature Range	-25 – 105 °C [-13 – 221 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	900
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211)



Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB




TE Part # CAT-AM705-CH8173
AMP MCP, UNSEALED CONNECTOR HOUSING


Also in the Series | AMP MCP 1.5K



Automotive Connector Caps & Covers (1)



Automotive Housings(103)




Insertion & Extraction Tools(1)

Also in the Series | AMP MCP 2.8




Automotive Connector Caps & Covers (1)



Automotive Connector Locks & Position Assurance(6)



Automotive Headers(1)



Automotive Housings(179)



Automotive Seals & Cavity Plugs(1)



Automotive Terminals(6)



Insertion & Extraction Tools(6)




Module Components(1)

Also in the Series | **AMP MCP Connector System**



Automotive Connector Caps & Covers (24)



Automotive Connector Locks & Position Assurance(8)




Automotive Headers(29)



Automotive Housings(352)



Automotive Seals & Cavity Plugs(6)



Automotive Terminals(124)



Insertion & Extraction Tools(13)



Other Automotive Connector Accessories(2)

Customers Also Bought



TE Part #1445022-6
MICRO MNL RFECEPT HSG SINGLE R



TE Part #173722-1
187 PL EX REC. 26-20AWG PTBR



TE Part #DTM06-6S-E007
DEUTSCH DTM HOUSINGS



TE Part #1563719-1
MCON, RECEPTACLE AND TAB



TE Part #1241846-2
TIMER, RECEPTACLE AND TAB



TE Part #1703034-1
AMP MCP, SFC, RECEPTACLE



TE Part #1-794606-2
MICRO MNL RPT CNT STRP 30AU LF



TE Part #1456968-6
CONTACT,FEMALE, 0.64, 0.35SQMM, AG



TE Part #1394416-1
TIMER, CONNECTOR HOUSING

Documents

Product Drawings

12 POS MALE HOUSING ASS'Y

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_284858-1_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_284858-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_284858-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



12 POS. HYBRID CONNECTOR UNSEALED FOR AMPMCP 1.5 AND 2.8 CONTACTS

English

12 POS. HYBRID CONNECTOR UNSEALED FOR AMPMCP 1.5 AND 2.8 CONTACTS

English

Instruction Sheets

12POS. AMPMCP1.5AND 2.8 MALE AND FEMALE HYBRID UNSEALED CONNECTOR

English

Instruction Sheet (non U.S.)

English