

1241380-1 ✓ ACTIVE

AMP | AMP MCP Connector System

TE Internal #: 1241380-1

Automotive Terminals, Receptacle, Mating Tab Width .059 in [1.5 mm], Tab Thickness .024 in [.6 mm], 20 – 17 AWG Wire Size, AMP MCP Connector System

[View on TE.com >](#)



Terminals & Splices > Automotive Terminals > AMP MCP, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: 1.5 mm [.059 in]

Mating Tab Thickness: .6 mm [.024 in]

Terminal Transmits: 0 – 24 A (Low Power)

Wire Size: 20 – 17 AWG

[All AMP MCP, RECEPTACLE AND TAB \(125\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	Yes
Primary Locking Feature	Locking Lance

Body Features

Terminal Seal Type	Single Wire Seal (SWS)
--------------------	------------------------

Contact Features

Contact Size	1.5K
Contact Fabrication	Stamped & Formed
Typical Current Rating	12 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	1.5 mm [.059 in]



Mating Tab Thickness	.6 mm[.024 in]
Interface Plating	Tin (Sn)
Contact Termination Area Plating Material	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Wire Size	.5 – 1 mm ²
Wire Size Search	17 AWG, 18 AWG, 19 AWG, 20 AWG
Wire Insulation Diameter	1.4 – 2.1 mm[.055 – .083 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Agency/Standard	LV214
-----------------	-------

Packaging Features

Packaging Method	Reel
Packaging Quantity	4500

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2022 (224)
 Candidate List Declared Against: JUNE 2022 (224)
 Does not contain REACH SVHC

Halogen Content
 Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability
 Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-H3399-CH8172
 Heavy Duty Sealed Connector Series Housings



TE Part # CAT-L489-CH8172
 LEAVYSEAL HOUSINGS



TE Part # CAT-AM705-CH8172
 AMP MCP, SEALED CONNECTOR HOUSING



TE Part # 1-1579007-1
 EXTRACTION TOOL



TE Part # 964972-1
 EINZELLEITERDICHUNG



TE Part # 963530-1
 EINZELLEITERDICHUNG



TE Part # 2305570-1
 Strip Terminal Cutter-Side Feed-No Crimp



TE Part # CAT-T4827-CH8172
 TIMER, CONNECTOR HOUSING




TE Part # 2278706-8
6POS, AMP MCP 1.5K, REC HSG, ASSY



TE Part # 1-1823440-1
22POS, MIXED, REC HSG, ASSY, SEALED



TE Part # 1-2293551-1
62POS, MIXED, REC HSG, ASSY, SLD



TE Part # 1579008-9
INSERTION TOOL



TE Part # 2-2151064-1
OCEAN_2.0_APPLICATOR-S-070F125O



TE Part # 2-2151064-2
OCEAN_2.0_APPLICATOR-S-070F125O



TE Part # 2-2293551-1
62POS, MIXED, REC HSG, ASSY, SLD



TE Part # 2063524-1
SDE MCP1.5 0.2-1.0mm2 ASSY



TE Part # 2063524-2
SDE MCP1.5 0.2-1.0mm2 DIE SET



TE Part # 2151064-1
OCEAN_2.0_APPLICATOR-S-070F125O



TE Part # 2151064-2
OCEAN_2.0_APPLICATOR-S-070F125O



TE Part # 2299987-1
65W PLUG ASSEMBLY


Also in the Series | AMP MCP Connector System




Automotive Connector Caps & Covers (24)




Automotive Connector Locks & Position Assurance (7)




Automotive Housings (352)




Automotive Seals & Cavity Plugs (6)



Automotive Terminals (125)



Insertion & Extraction Tools (13)



Other Automotive Connector Accessories (2)



PCB Headers & Receptacles (29)

Documents



Product Drawings

[AMP MCP 1.5K, CONTACT, SWS](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1241380-1_B_c-1241380-1-b.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1241380-1_B_c-1241380-1-b.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1241380-1_B_c-1241380-1-b.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HDSCS Catalog](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

German