

Group markers
WAD 4 GE BED

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WAD 4 GE BED
Order No.	1072000000
GTIN (EAN)	4008190446109
Qty.	50 pc(s).

Data sheet

Group markers WAD 4 GE BED

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	4.5 mm	Width (inches)	0.177 inch
Height	19.8 mm	Height (inches)	0.78 inch
Depth	9.6 mm	Depth (inches)	0.378 inch
Net weight	0.244 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-2		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Snap-on		

Dimensions

Pitch in mm (P)	4 mm
-----------------	------

Classifications

ETIM 3.0	EC000897	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC002848
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-45
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-92		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP