Product data sheet Characteristics

BMXAMO0410

isolated analog output module X80 - 4 outputs





Main

| Range of product | Modicon X80 |
|----------------------------|----------------------|
| Product or component type | Analog output module |
| Electrical connection | 20 ways 1 connector |
| Isolation between channels | Isolated |

Complementary

| Complementary | | |
|-------------------------------|--|--|
| Measurement error | <= 0.2 % of full scale 060 °C 0.1 % of full scale 25 °C | |
| Temperature drift | 45 ppm/°C +/- 10 V 45 ppm/°C 020 mA 45 ppm/°C 420 mA | |
| Minimum crosstalk attenuation | 80 dB | |
| Common mode rejection | 100 dB | |
| Isolation voltage | 1400 V DC between channels and ground 1400 V DC between channels and bus 750 V DC between channels | |
| Detection type | Open circuit 020 mA Open circuit 420 mA Short circuit +/- 10 V | |
| Load impedance ohmic | >= 1000 Ohm +/- 10 V <= 500 Ohm 020 mA <= 500 Ohm 420 mA | |
| Output level | High level | |
| Analogue output number | 4 | |
| Analogue output type | Current: 020 mA Current 420 mA Voltage +/- 10 V | |
| Analogue output resolution | 15 bits + sign | |
| Supply | Internal power supply via rack | |
| Conversion time | <= 1 ms | |
| Maximum conversion value | 021 mA 020 mA 021 mA 420 mA +/- 10.5 V +/- 10 V | |
| Fallback mode | Configurable Predefined | |
| Operating altitude | 02000 m 20005000 m with derating factor | |
| Status LED | RUN 1 LED Green) 1 LED per channel (green)channel diagnostic ERR 1 LED Red) I/O 1 LED Red) | |
| Net Weight | 0.33 lb(US) (0.15 kg) | |
| Power consumption in W | 3 W 24 V DC typical 3.6 W 24 V DC maximum 0.45 W 3.3 V DC typical 0.51 W 3.3 V DC maximum | |

Environment

| Vibration resistance | 3 gn | |
|---------------------------------------|---|--|
| Shock resistance | 30 gn | |
| Ambient air temperature for storage | -40185 °F (-4085 °C) | |
| Ambient air temperature for operation | 32140 °F (060 °C) | |
| Relative humidity | 595 % 131 °F (55 °C) without condensation | |
| IP degree of protection | IP20 | |
| Directives | 2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility 2012/19/EU - WEEE directive | |
| Product certifications | CE RCM CSA EAC Merchant Navy UL | |
| Standards | EN/IEC 61010-2-201 EN/IEC 61131-2 UL 61010-2-201 CSA C22.2 No 61010-2-201 | |

Ordering and shipping details

| or doring direct onlyping dottane | |
|-----------------------------------|-----------------------|
| Category | 18160 - MODICON M340 |
| Discount Schedule | PC34 |
| GTIN | 00785901632726 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.47 lb(US) (0.21 kg) |
| Returnability | Yes |
| Country of origin | FR |

Packing Units

| 1 doking office | |
|------------------------------|-----------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 2.17 in (5.5 cm) |
| Package 1 width | 4.33 in (11 cm) |
| Package 1 Length | 4.72 in (12 cm) |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 15 |
| Package 2 Weight | 7.96 lb(US) (3.61 kg) |
| Package 2 Height | 5.91 in (15 cm) |
| Package 2 width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |
| | |

Offer Sustainability

| Sustainable offer status | Green Premium product | |
|----------------------------|---|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | |
| REACh Regulation | [™] REACh Declaration | |
| REACh free of SVHC | Yes | |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EEU RoHS Declaration | |
| Mercury free | Yes | |
| RoHS exemption information | ₫Yes | |
| China RoHS Regulation | ☑ China RoHS Declaration | |
| Environmental Disclosure | Product Environmental Profile | |


| Circularity Profile | End Of Life Information | |
|----------------------|--|--|
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. | |
| Contractual warranty | | |
| Warranty | 18 months | |

Product data sheet **Dimensions Drawings**

BMXAMO0410

Modules Mounted on Racks

Dimensions




- With removable terminal block (cage, screw or spring). With FCN connector.
- On AM1 ED rail: 35 mm wide, 15 mm deep. Only possible with BMXXBP0400/0400H/0600/0600H/0800/0800H rack.

| Rack references | a in mm | a in in. |
|----------------------------|---------|----------|
| BMXXBP0400 and BMXXBP0400H | 242.4 | 09.54 |
| BMXXBP0600 and BMXXBP0600H | 307.6 | 12.11 |
| BMXXBP0800 and BMXXBP0800H | 372.8 | 14.68 |
| BMXXBP1200 and BMXXBP1200H | 503.2 | 19.81 |

BMXAMO0410

Wiring Diagram



U/lx + pole input for channel x COMx pole input for channel x Chan**N**elltage actuator

0116

Chan@irrent actuator

1

The current loop is self-powered by the output and does not request any external supply.