

angular milling cutter, 90°, with thread

For milling inserts AP.. 0602..

ATORN[®]

Application

For universal use in all materials.

Version

- With screw-in thread
- Wear-resistant, nickel-plated version
- Internal cooling
- Clamping screw tightening torque (indexable insert) M1.8 = 0.7 Nm



Art. No.	16017 712
Cutting edge diameter	12 mm
Clearance length	16 mm
Length	16 mm
Thread dimension	M6
max. ap	5.2 mm
Number of cutting edges	3 PCS

EAN-Code

4050293433890

