

Surface chuck (Weldon)

In accordance with ISO 12164 (DIN 69893); with sealable coolant bores

ORION[®]

Application:

for clamping tools with straight shanks and clamping surfaces in line with DIN 1835 B.

Execution:

- All tapers and tolerances are precision-ground.
- Taper tolerance AT3.
- Strength HRC 57-60.
- Core strength 1,000-1,200 N/mm².
- With Balluff chip hole.
- All functional surfaces machined.

Advantage:

- Prevents the tool from slipping while maintaining high concentricity.

Delivery:

1x surface chuck (Weldon) in accordance with ISO 12164 (DIN 69893) with sealable coolant bores.



Art. no.	23157 505
Brand	ORION
Manufacturer Part Number	23157505
Tool holding device	HSK 63
Clamping diameter	8 mm
Projecting length	100 mm
Outer diameter	28 mm
Balancing quality	G 2.5 at 25 rpm
Gross Weight	1.036 kg
Product Group	2AV

EAN

4053625398850